

PDU, 0U, 60A(48A)NA/63A Int, 380-415V, 3P Wye, 12 CB (18)C13 (18)4-in-1

Data Solutions

KATALOGNUMMER

EB09JA

The Basic PDU is a cost-effective, reliable power distribution solution. Premium hydraulic-magnetic circuit breakers operate consistently in high-temperature environments. The Basic PDU offers advanced features, such as color-coded locking IEC outlets, a slim chassis design, and toolless mounting backed by a 5-year hassle-free warranty.

FUNKTIONER

Black Powder Coated Chassis

IEC 62368 listed. RoHS, and REACH compliant. See drawing for additional information.

PRODUKTEGENSKABER

Produktfamilie: Enlogic

Type: Basic PDU

Product Type: Socket Strip

Stiktype: (18) C13/C15; (18) C13/C15/C19/C21

Socket Quantity: 36

Farve: Black

Switched Outlets: No

Cable Length: 1800mm

Circuit Breaker: 20 A, 1-pole, Hy-MagA

Power Rating: 34.6 kVA North America; 43.5 kVA International

Circuit Breaker Quantity: 12

Nominal Power Output: 230VAC

Nominal spænding: 415V

Number of Output Voltages: 36

On/Off Switch Included: No

Amperage (Derated Amperage): 60 A (48 A) North America; 63 A International

Output Voltage: 208 – 230VAC

Rack Units: 0U

Plug Type: IEC 60309 560P6/563P6

Metering Type: None

Removable Input Cable: No

Materiale: Stål

Finish: Struktur Pulvermaling

Højde: 965mm

Bredde: 114mm

Dybde: 75mm

Pakke mængde: 1

Input Cable Length: 1.8m

YDERLIGERE PRODUKTOPLYSNINGER

Warranty : nVent Enlogic branded equipment provided shall be free from manufacturing defects for a period of five (5) years from the invoice date to the original purchaser.

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.



Vores kraftfulde portefølje af mærker:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE