

# Intelligent iPDU, EN5810, 400 VAC, 3-PH, 32 A

## Data Solutions

### KATALOGNUMMER

**EN5810**



Modular, compact intelligent PDU with inlet metering. Ultra-Low Profile Design

### FUNKTIONER

Enlogic EN5xxx Intelligent Power Distribution Units monitors input power of the entire PDU and individual outlet monitoring, provides billing grade unit level monitoring

High Visibility Data Display and Interactive Graphic Display

Measure circuit breaker loads across redundant feeds to avoid accidental downtime

Enables smart load balancing for power efficiency and maximized capacity utilization

Gigabit Ethernet Interface and redundant Ethernet (10/100)

iPDU DC power redundancy solution for up to 64 PDU's

Toolless Hot-Swap Controller

Input voltage 400 VAC, 3-phase

C13, C19 outlets

### PRODUKTEGENSKABER

Produktfamilie: Enlogic

Type: Intelligent PDU

Product Type: Socket Strip

Stiktype: (24) C13; (12) C19

Socket Quantity: 36

Farve: Black

Switched Outlets: No

Circuit Breaker: 16 A, 1-pole, Hy-Mag

Power Rating: 22.0 kVA

Circuit Breaker Quantity: 6

Input Cable Location: Top Feed

Input Voltage: 380 – 415V

Phase: 3 PH

Nominel spænding: 415V

Max Power Input: 22.0 kVA

On/Off Switch Included: No

Amperage (Derated Amperage): 32 A

Output Voltage: 230VAC

Rack Units: 0U

Plug Type: IEC 60309 532P6 (IP44)

Metering Type: Outlet

Removable Input Cable: No

Materiale: Stål

Finish: Struktur Pulvermaling

Højde: 1780mm

Bredde: 85mm

Dybde: 53mm

Vægt: 12.23kg

Pakke mængde: 1

Input Cable Length: 3m

## YDERLIGERE PRODUKTOPLYSNINGER

---

Please order bracket for vertical mounting separately.

## ADVARSEL

---

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer.

Vejledninger er tilgængelige på [www.nvent.com](http://www.nvent.com) og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.



Vores kraftfulde portefølje af mærker:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**