


# CABS Module Kit with Neutral



## CERTIFICERINGER



## FUNKTIONER

Modules provide flexibility to select distance between phases and supports

Installs quickly and easily

Halogen free insulators

RoHS compliant

## SPECIFIKATIONER

<b>Typical Application Current Rating:</b>	400 - 4500 A
<b>Max Working Voltage, IEC (Ui):</b>	1000;1500
<b>Working Temperature:</b>	-40 to 130 °C
<b>Finish:</b>	Electrogalvanized
<b>Materiale:</b>	Stål;Glass Fibre Reinforced Polyamide
<b>Complies With:</b>	IEC® 60439.1;IEC® 61439.1;IEC® 60695-2-11 (Glow Wire Test 960 °C)
<b>Flammability Rating:</b>	UL® 94V-0

Table 1/2

Katalognummer	Artikelnummer	Busbars per Phase	Busbar Width	Busbar Thickness	Dybde (D)	Width (W)
---------------	---------------	-------------------	--------------	------------------	-----------	-----------

CABS4-5TN-MOD	549340	1 - 4	30 - 125 mm	5 mm	39mm	75 mm
CABS2-10TN-MOD	549350	1 - 2	30 - 120 mm	10 mm	39mm	75 mm
CABS3-10TN-MOD	549360	1 - 3	30 - 120 mm	10 mm	39mm	100 mm

Table 2/2

Katalognummer	Artikelnummer	Unit Weight
CABS4-5TN-MOD	549340	0.5 kg
CABS2-10TN-MOD	549350	0.48 kg
CABS3-10TN-MOD	549360	0.58 kg

## YDERLIGERE PRODUKTOPLYSNINGER

CABS modules must be installed on CABS-APP Aluminium Profile.

## DIAGRAMS



## ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på [www.nvent.com](http://www.nvent.com) og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden unladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

**North America**

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

**Europe**

Netherlands:

+31 800-0200135

France:

+33 800 901 793

**Europe**

Germany:

800 1890272

Other Countries:

+31 13 5835404

**APAC**

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Vores kraftfulde portefølje af mærker:

**CADDY**

**ERICO**

**HOFFMAN**

**ILSCO**

**SCHROFF**

**TRACHTE**