

19" Assembly Kit M6

For standard grounding use a grounding nut and washer on at least one attachment point.

When 19" assembly kit is used with conductive 19" panel mount, grounding cage nuts are not needed.



CERTIFICERINGER



FUNKTIONER

Assembly kits for assembly of 19" components into a cabinet

For mounting of front panels, distribution fields or other components on the frame, slide mounts or depth members with square cut-outs

SPECIFIKATIONER

Product Type: Assembly Kit

Finish: Forzinket Stål

Table 1/2

Katalognummer	Length	Pakke mængde	Thread Size	Materiale	Produktfamilie	Type
21120-196	16mm	4	M6	Stål		Mounting Kit, Grounding

Katalognummer	Length	Pakke mængde	Thread Size	Materiale	Produktfamilie	Type
21190-095		4	M6	Stål, ABS	RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, Comptec, Inpac, MultipacPRO, Varistar CP, Eurorack, Outdoor	Mounting Kit
21120-213		4	M6	Stål		Mounting Kit
21100-435		8	M6	Stål, ABS	RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, Comptec, Inpac, MultipacPRO, Varistar CP, Novastar, Eurorack, Outdoor	Mounting Kit
21120-199	13mm	100	M6	Stål		Mounting Kit, Grounding
21120-197	16mm	32	M6	Stål		Mounting Kit, Grounding
21120-198	16mm	50	M6	Stål		Mounting Kit, Grounding
21190-435		32	M6	Stål, ABS	RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, Comptec, Inpac, MultipacPRO, Varistar CP, Eurorack, Outdoor	Mounting Kit

Katalognummer	Length	Pakke mængde	Thread Size	Materiale	Produktfamilie	Type
21101-810		100	M6	Stål, ABS	RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, Comptec, Inpac, MultipacPRO, Varistar CP, Novastar, Eurorack, Outdoor	Mounting Kit
21101-809		50	M6	Stål, ABS	RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, Comptec, Inpac, MultipacPRO, Varistar CP, Novastar, Eurorack, Outdoor	Mounting Kit
21120-215		32	M6	Stål		Mounting Kit
21120-214		50	M6	Stål		Mounting Kit
21120-216		100	M6	Stål		Mounting Kit

Table 2/2

Katalognummer	Works With	Certificeringer
21120-196	Front Panels, Eurorack, Novastar, Varistar, Varistar CP	
21190-095	19" Cases, 19" Wallmount, 19" Indoor Cabinets, 19" Outdoor Cabinets	RoHS
21120-213	Front Panels, Eurorack, Novastar, Varistar, Varistar CP	
21100-435	19" Cases, 19" Wallmount, 19" Indoor Cabinets, 19" Outdoor Cabinets	RoHS
21120-199	Front Panels, Eurorack, Novastar, Varistar, Varistar CP	
21120-197	Front Panels, Eurorack, Novastar, Varistar, Varistar CP	
21120-198	Front Panels, Eurorack, Novastar, Varistar, Varistar CP	
21190-435	19" Cases, 19" Wallmount, 19" Indoor Cabinets, 19" Outdoor Cabinets	RoHS

Katalognummer	Works With	Certificeringer
21101-810	19" Cases, 19" Wallmount, 19" Indoor Cabinets, 19" Outdoor Cabinets	RoHS
21101-809	19" Cases, 19" Wallmount, 19" Indoor Cabinets, 19" Outdoor Cabinets	RoHS
21120-215	Front Panels, Eurorack, Novastar, Varistar, Varistar CP	
21120-214	Front Panels, Eurorack, Novastar, Varistar, Varistar CP	
21120-216	Front Panels, Eurorack, Novastar, Varistar, Varistar CP	

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden unkladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE