

Interscale for Embedded NUC, Conduction Cooled, 34 mm, 112, mm 107 mm

KATALOGNUMMER

14820-701



Small form factor case with integrated EMC-shielding and conduction cooling for eNUC boards, based on the innovative and flexible nVent SCHROFF Interscale platform.

CERTIFICERINGER



FUNKTIONER

Modular case consisting of 3 easy to assemble parts; body, topcover and front panel

Integrated EMC protection

Compliant with the SDT.03 embeddedNUC standard <http://www.sget.org/standards.html>

Cutouts specific for IES MB95 embeddedNUC board (<http://en.ies.de/>)

Rigid construction requires only two screws

Perforated side panels for passive cooling

Board mounting studs installed

Color RAL 7016

Other dimensions, cutout shapes or locations and screenprinting available

PRODUKTEGENSKABER

Product Type: Small Form Factor Case

Produktfamilie: Interscale

Type: Desktop

Højde: 34mm

Bredde: 112mm

Dybde: 106.5mm

Materiale: Aluminium

Farve: Anthracite Grey

Farvekode: RAL 7016

Finish: Struktur Pulvermaling

Beskyttelsesgrad: IP20

Cooling: Perforated

Pakke mængde: 1

Net Weight: 0.175kg

YDERLIGERE PRODUKTOPLYSNINGER

Modified or customized cases upon request.

Only the listed Interscale accessories are compatible.

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden unladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vores kraftfulde portefølje af mærker:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE