

# Snap in cable management finger kit

## KATALOGNUMMER

**24630-057**



The hand mountable cable fingers ensure an optimal cable radius and prevent damage or breakage by ensuring an appropriate cable bend radius. The flexible T shaped structures protect the cables so that the structured cabling system remains undamaged and fully functional.

## FUNKTIONER

T-shaped cable fingers installable directly on the 19" panel mounts without screws allow for easy and clean management of copper and fiber optic cables, etc.

Each 5-Finger unit can be individually snapped on to the 19" upright based on the cable management requirements

The cable fingers protrude 81,5mm from the 19" upright, hence needs a minimum recess of ~82mm

Finger spacing of 36,45mm for high density cabling

Works only with Datacom 19" uprights / panel mounts with printed U Height identification - 24630013, 24630014 and 24630015

## PRODUKTEGENSKABER

Product Type: Cable Support

Produktfamilie: Varistar CP

Type: Finger Kit

Materiale: PVC

Farve: Black

Pakke mængde: 20

Net Weight: 1.98kg

## YDERLIGERE PRODUKTOPLYSNINGER

Easy snap in kit for cable management, allows customers to build the cable finger duct using smaller units

## ADVARSEL

---

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på [www.nvent.com](http://www.nvent.com) og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden unndladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab  
Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Vores kraftfulde portefølje af mærker:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**