



Horizontal Rail, Rear, Type H-VT, Heavy, 1000 mm

KATALOGNUMMER

34560-701



Combinations of horizontal rails and side panels

		+ ¹ can be combined		+ combination not recommended			
100% / 1.0		-	+	+	+	+	recommended for support
		+	recommended for flexible (not for heavy)	+	recommended for heavy and supported for heavy	+	+
100% / 1.0		+	recommended for light	+	recommended for flexible	-	-
		+	+	-	-	-	-
100% / 1.0		+	+	+	+	+	+
		+	+	+	+	+	+
100% / 1.0		+	+	+	+	+	+
		+	+	+	+	+	+
100% / 1.0		+	+	+	+	+	+
		+	+	+	+	+	+

The horizontal rail, type VT enables the direct assembly of a backplane.

CERTIFICERING



FUNKTIONER

For direct backplane mounting

Mounting top and bottom

Recessed installation for high mechanical demands (H-VT)

Aluminum extrusion, anodized finish, conductive contact surface

PRODUKTEGENSKABER

Rack Width: 195HP

Pakke mængde: 1

Finish: Anodized

Length: 1000mm

Materiale: Aluminium

Produktfamilie: EuropacPRO; RatiopacPRO; RatiopacPRO AIR; CompacPRO; PropacPRO

Product Type: Horizontal Rail

Type: Heavy, VT

Works With: Subracks; Cases

Net Weight: 0.332kg

YDERLIGERE PRODUKTOPLYSNINGER

Delivery is in standard pack multiples. Pricing is per individual item.

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vores kraftfulde portefølje af mærker:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE