

# Horizontal Rail, Front, Type R-LD, Rugged, Long Lip , 1000 mm

**KATALOGNUMMER**

**34566-301**



## Combinations of horizontal rails and side panels

$\bullet$  = can be combined       $\bullet$  = combination not recommended

| Support type | Horizontal rail                                                                     | Side panel                                                                          | Combination |
|--------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------|
| Support 1.0  |    |    | +           |
| Support 1.0  |    |    | +           |
| Support 1.0  |    |    | +           |
| Support 1.0  |    |    | +           |
| Support 1.0  |    |    | +           |
| Support 1.0  |    |    | +           |
| Support 1.0  |    |    | +           |
| Support 1.0  |  |  | +           |
| Support 1.0  |  |  | +           |
| Support 1.0  |  |  | +           |
| Support 1.0  |  |  | +           |
| Support 1.0  |  |  | +           |
| Support 1.0  |  |  | +           |
| Support 1.0  |  |  | +           |
| Support 1.0  |  |  | +           |
| Support 1.0  |  |  | +           |
| Support 1.0  |  |  | +           |
| Support 1.0  |  |  | +           |
| Support 1.0  |  |  | +           |
| Support 1.0  |  |  | +           |
| Support 1.0  |  |  | +           |
| Support 1.0  |  |  | +           |
| Support 1.0  |  |  | +           |
| Support 1.0  |  |  | +           |
| Support 1.0  |  |  | +           |
| Support 1.0  |  |  | +           |
| Support 1.0  |  |  | +           |
| Support 1.0  |  |  | +           |
| Support 1.0  |  |  | +           |
| Support 1.0  |  |  | +           |
| Support 1.0  |  |  | +           |
| Support 1.0  |  |  | +           |
| Support 1.0  |  |  | +           |
| Support 1.0  |  |  | +           |
| Support 1.0  |  |  | +           |
| Support 1.0  |  |  | +           |
| Support 1.0  |  |  | +           |
| Support 1.0  |  |  | +           |
| Support 1.0  |  |  | +           |
| Support 1.0  |  |  | +           |
| Support 1.0  |  |  | +           |

The rugged horizontal rail type can handle shock and vibration up to 25 g. It enables the use of IEEE handles.

## CERTIFICERINGER



## FUNKTIONER

Type R-LD "rugged" horizontal rails with 3-hole fixing for increased robustness

For insertion/extraction of CompactPCI or, VME64x boards

With HP units printed from 28 HP upwards

Length 20, 28, 40, 42, 63, 84 HP or 1000 mm

Aluminum extrusion, anodized finish, conductive contact surface, with HP markings

## PRODUKTEGENSKABER

Rack Width: 195HP

Pakke mængde: 1

Finish: Anodized

Length: 1000mm

Materiale: Aluminium

Produktfamilie: EuropacPRO

Product Type: Horizontal Rail

Type: Rugged, LD

Works With: Subracks

Net Weight: 0.6kg

## ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på [www.nvent.com](http://www.nvent.com) og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab  
Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Vores kraftfulde portefølje af mærker:

**CADDY**

**ERICO**

**HOFFMAN**

**ILSCO**

**SCHROFF**

**TRACHTE**