

Interscale Desktop Case, Perforated



Flexible desktop case with integrated EMC protection and perforated sides. Based on the nVent SCHROFF Interscale platform and developed in accordance with IEC 60297-3-109.

CERTIFICERINGER



FUNKTIONER

Modular desktop case consisting of 4 assembled parts

Developed according to IEC 60297-3-109 (under progress at IEC)

Integrated EMC protection

Ingress protection up to IP 20

Color RAL 7016

Modified or customized cases upon request

SPECIFIKATIONER

Materiale:	Aluminium; Stål
Type:	Desktop
Produktfamilie:	Interscale
Beskyttelsesgrad:	IP20
Farvekode:	RAL 7016
Product Type:	Small Form Factor Case

Table 1/2

Katalognummer	Højde	Pakke mængde	Bredde	Dybde	Cooling	Farve
14825-154	43.7mm	1	221mm	177mm	Perforated	Anthracite Grey
14825-254	88.1mm	1	221mm	177mm	Perforated	Anthracite Grey
14825-255	88.1mm	1	221mm	221mm	Perforated	Anthracite Grey
14825-197	43.7mm	1	399mm	310mm	Perforated	Anthracite Grey
14825-275	88.1mm	1	310mm	221mm	Perforated	Anthracite Grey
14825-195	43.7mm	1	399mm	221mm	Perforated	Anthracite Grey
14825-295	88.1mm	1	399mm	221mm	Perforated	Anthracite Grey
14825-297	88.1mm	1	399mm	310mm	Perforated	Anthracite Grey
14825-175	43.7mm	1	310mm	221mm	Perforated	Anthracite Grey
14825-375	132.6mm	1	310mm	221mm	Perforated	Anthracite Grey
14825-395	132.6mm	1	399mm	221mm	Perforated	Anthracite Grey
14825-155	43.7mm	1	221mm	221mm	Perforated	Anthracite Grey
14825-397	132.6mm	1	399mm	310mm	Perforated	Anthracite Grey

Table 2/2

Katalognummer	Finish
14825-154	Aluminum-Zinc Plated, Struktur Pulvermaling
14825-254	Aluminum-Zinc Plated, Struktur Pulvermaling
14825-255	Aluminum-Zinc Plated, Struktur Pulvermaling
14825-197	Aluminum-Zinc Plated, Struktur Pulvermaling
14825-275	Aluminum-Zinc Plated, Struktur Pulvermaling
14825-195	Aluminum-Zinc Plated, Struktur Pulvermaling
14825-295	Aluminum-Zinc Plated, Struktur Pulvermaling
14825-297	Aluminum-Zinc Plated, Struktur Pulvermaling
14825-175	Aluminum-Zinc Plated, Struktur Pulvermaling
14825-375	Aluminum-Zinc Plated, Struktur Pulvermaling
14825-395	Aluminum-Zinc Plated, Struktur Pulvermaling
14825-155	Aluminum-Zinc Plated, Struktur Pulvermaling
14825-397	Aluminum-Zinc Plated, Struktur Pulvermaling

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vores kraftfulde portefølje af mærker:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE