

# Varistar CP Cabeling Rack



Welded steel frame for high static load requirements.  
Prepared for high cable densities and 19" integration.

## FUNKTIONER

Preconfigured, ready to use cabinet

Static load-carrying capacity up to 1600 kg

Ingress protection class IP 20

Installation of different Networking equipment possible

Integrated vertical and horizontal cable management

Can be easily integrated into aisle containment system

## SPECIFIKATIONER

**Product Type:** Rack

**Materiale:** Stål

**Frame Material:** Stål

Table 1/3

Katalognummer	Rack Height	Cladding Material	Frame Color	Højde	Frame Color Code	Cladding Color
10630-027	42U	Stål	Black Grey	2000mm	RAL 7021	Black Grey
10630-028	42U	Stål	Black Grey	2000mm	RAL 7021	Black Grey

Table 2/3

Katalognummer	Bredde	Dybde	Static Load	Cladding Color Code	Pakke mængde	Dynamic Load
---------------	--------	-------	-------------	---------------------	--------------	--------------

10630-027	800mm	1200mm	1600kg	RAL 7021	1	1000kgf
10630-028	800mm	1200mm	1600kg	RAL 7021	1	1000kgf

Table 3/3

Katalognummer	Finish
10630-027	Struktur Pulvermaling
10630-028	Struktur Pulvermaling

## ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på [www.nvent.com](http://www.nvent.com) og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden unkladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Vores kraftfulde portefølje af mærker:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**