

# MultipacPRO Mounting Plate



Mounting plates are designed for the mounting of heavy components, e.g. transformers.

## CERTIFICERINGER



## FUNKTIONER

Mounting plates are designed for the mounting of heavy components, e.g. transformers

Bolted laterally inside on a 19" chassis

## SPECIFIKATIONER

|                        |                |
|------------------------|----------------|
| <b>Materiale:</b>      | Aluminium      |
| <b>Works With:</b>     | Chassis        |
| <b>Product Type:</b>   | Mounting Plate |
| <b>Produktfamilie:</b> | MultipacPRO    |

Table 1/1

| Katalognummer | Dybde | Pakke mængde | Rack Width | Bredde  | Certificeringer |
|---------------|-------|--------------|------------|---------|-----------------|
| 20860-107     | 150mm | 1            | 84HP       | 402.5mm | RoHS            |
| 20860-112     | 450mm | 1            | 84HP       | 402.5mm |                 |
| 20860-111     | 390mm | 1            | 84HP       | 402.5mm | RoHS            |
| 20860-108     | 210mm | 1            | 84HP       | 402.5mm | RoHS            |
| 20860-110     | 330mm | 1            | 84HP       | 402.5mm | RoHS            |
| 20860-109     | 270mm | 1            | 84HP       | 402.5mm | RoHS            |

## YDERLIGERE PRODUKTOPLYSNINGER

---

Mounting plates can also be fitted at the same time as the internal mounting for euroboards.

Where a mounting plate is used the clear mounting height is reduced by at least 2.5 mm.

## ADVARSEL

---

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på [www.nvent.com](http://www.nvent.com) og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab  
Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Vores kraftfulde portefølje af mærker:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**