

Varistar CP Side Panel, Screw-Fixed

Screw assembly side panel for Varistar CP cabinet.



FUNKTIONER

Screw fixed, Robust and Single person mountable Side Panel

Side panel without grounding kit

SPECIFIKATIONER

Product Type: Cabinet/Rack Panel

Table 1/5

Katalognummer	Rack Height	Højde	Dybde	Beskyttelsesgrad	Pakke mængde	Farve
21630-266	29U	1400mm	800mm	IP20	2	Black Grey
21630-278	42U	2000mm	600mm	IP20	2	Black Grey
21630-231	33U	1600mm	900mm	IP55	2	Black Grey
21630-079	42U	2000mm	1200mm	IP55	2	Black Grey
21630-238	42U	2000mm	600mm	IP55	2	Black Grey
21630-226	29U	1400mm	800mm	IP55	2	Black Grey
21630-271	33U	1600mm	900mm	IP20	2	Black Grey
21630-279	42U	2000mm	800mm	IP20	2	Black Grey
21630-228	29U	1400mm	1000mm	IP55	2	Black Grey
21630-268	29U	1400mm	1000mm	IP20	2	Black Grey
21630-239	42U	2000mm	800mm	IP55	2	Black Grey
21630-081	47U	2200mm	1100mm	IP55	2	Black Grey

Katalognummer	Rack Height	Højde	Dybde	Beskyttelsesgrad	Pakke mængde	Farve
21630-227	29U	1400mm	900mm	IP55	2	Black Grey
21630-272	33U	1600mm	1000mm	IP20	2	Black Grey
21630-280	42U	2000mm	900mm	IP20	2	Black Grey
21630-267	29U	1400mm	900mm	IP20	2	Black Grey
21630-264	24U	1200mm	1000mm	IP20	2	Black Grey
21630-082	47U	2200mm	1200mm	IP55	2	Black Grey
21630-240	42U	2000mm	900mm	IP55	2	Black Grey
21630-224	24U	1200mm	1000mm	IP55	2	Black Grey

Table 2/5

Katalognummer	Rack Height	Højde	Dybde	Beskyttelsesgrad	Pakke mængde	Farve
21630-927	24U	1200mm	900mm	IP55	2	Black Grey
21630-225	29U	1400mm	600mm	IP55	2	Black Grey
21630-043	42U	2000mm	1000mm	IP20	2	Black Grey
21630-223	24U	1200mm	900mm	IP55	2	Black Grey
21630-241	42U	2000mm	1000mm	IP55	2	Black Grey
21630-263	24U	1200mm	900mm	IP20	2	Black Grey
21630-274	38U	1800mm	800mm	IP20	2	Black Grey
21630-270	33U	1600mm	800mm	IP20	2	Black Grey
21630-249	47U	2200mm	1100mm	IP55	2	Black Grey
21630-047	47U	2200mm	1100mm	IP20	2	Black Grey
21630-230	33U	1600mm	800mm	IP55	2	Black Grey
21630-048	47U	2200mm	1200mm	IP20	2	Black Grey
21630-243	42U	2000mm	1200mm	IP55	2	Black Grey
21630-273	38U	1800mm	600mm	IP20	2	Black Grey
21630-229	33U	1600mm	600mm	IP55	2	Black Grey
21630-045	42U	2000mm	1200mm	IP20	2	Black Grey
21630-242	42U	2000mm	1100mm	IP55	2	Black Grey
21630-233	38U	1800mm	600mm	IP55	2	Black Grey
21630-044	42U	2000mm	1100mm	IP20	2	Black Grey
21630-467	29U	1400mm	600mm	IP55	2	Black Grey

Table 3/5

Katalognummer	Rack Height	Højde	Dybde	Beskyttelsesgrad	Pakke mængde	Farve
21630-250	47U	2200mm	1200mm	IP55	2	Black Grey
21630-236	38U	1800mm	1000mm	IP55	2	Black Grey
21630-234	38U	1800mm	800mm	IP55	2	Black Grey
21630-276	38U	1800mm	1000mm	IP20	2	Black Grey
21630-235	38U	1800mm	900mm	IP55	2	Black Grey
21630-269	33U	1600mm	600mm	IP20	2	Black Grey
21630-078	42U	2000mm	1100mm	IP55	2	Black Grey
21630-277	42U	2000mm	300mm	IP20	2	Black Grey
21630-275	38U	1800mm	900mm	IP20	2	Black Grey
21630-237	42U	2000mm	300mm	IP55	2	Black Grey
21630-232	33U	1600mm	1000mm	IP55	2	Black Grey
21630-262	24U	1200mm	800mm	IP20	2	Black Grey
21630-933	38U	1800mm	900mm	IP55	2	Black Grey
21630-283	47U	2200mm	800mm	IP20	2	Black Grey
21630-478	47U	2200mm	600mm	IP55	2	Black Grey
21630-465	24U	1200mm	600mm	IP55	2	Black Grey
21630-477	47U	2200mm	300mm	IP55	2	Black Grey
21630-246	47U	2200mm	800mm	IP55	2	Black Grey
21630-077	42U	2000mm	1000mm	IP55	2	Black Grey
21630-284	47U	2200mm	900mm	IP20	2	Black Grey

Table 4/5

Katalognummer	Rack Height	Højde	Dybde	Beskyttelsesgrad	Pakke mængde	Farve
21630-931	33U	1600mm	900mm	IP55	2	Black Grey
21630-476	42U	2000mm	900mm	IP55	2	Black Grey
21630-930	29U	1400mm	1000mm	IP55	2	Black Grey
21630-475	42U	2000mm	800mm	IP55	2	Black Grey
21630-247	47U	2200mm	900mm	IP55	2	Black Grey
21630-471	38U	1800mm	600mm	IP55	2	Black Grey
21630-474	42U	2000mm	600mm	IP55	2	Black Grey
21630-046	47U	2200mm	1000mm	IP20	2	Black Grey
21630-932	33U	1600mm	1000mm	IP55	2	Black Grey
21630-473	42U	2000mm	300mm	IP55	2	Black Grey

Katalognummer	Rack Height	Højde	Dybde	Beskyttelsesgrad	Pakke mængde	Farve
21630-248	47U	2200mm	1000mm	IP55	2	Black Grey
21630-472	38U	1800mm	800mm	IP55	2	Black Grey
21630-221	24U	1200mm	600mm	IP55	2	Black Grey
21630-469	33U	1600mm	600mm	IP55	2	Black Grey
21630-928	24U	1200mm	1000mm	IP55	2	Black Grey
21630-050	52U	2450mm	1100mm	IP20	2	Black Grey
21630-468	29U	1400mm	800mm	IP55	2	Black Grey
21630-261	24U	1200mm	600mm	IP20	2	Black Grey
21630-265	29U	1400mm	600mm	IP20	2	Black Grey
21630-934	38U	1800mm	1000mm	IP55	2	Black Grey

Table 5/5

Katalognummer	Rack Height	Højde	Dybde	Beskyttelsesgrad	Pakke mængde	Farve
21630-281	47U	2200mm	300mm	IP20	2	Black Grey
21630-051	52U	2450mm	1200mm	IP20	2	Black Grey
21630-244	47U	2200mm	300mm	IP55	2	Black Grey
21630-049	52U	2450mm	1000mm	IP20	2	Black Grey
21630-222	24U	1200mm	800mm	IP55	2	Black Grey
21630-466	24U	1200mm	800mm	IP55	2	Black Grey
21630-080	47U	2200mm	1000mm	IP55	2	Black Grey
21630-929	29U	1400mm	900mm	IP55	2	Black Grey
21630-282	47U	2200mm	600mm	IP20	2	Black Grey
21630-480	47U	2200mm	900mm	IP55	2	Black Grey
21630-245	47U	2200mm	600mm	IP55	2	Black Grey
21630-479	47U	2200mm	800mm	IP55	2	Black Grey
21630-470	33U	1600mm	800mm	IP55	2	Black Grey

Table 1/5

Katalognummer	Farvekode	Finish	Materiale	Type
21630-266	RAL 7021	Struktur Pulvermaling	Stål	Side Panel, Screw Fixed
21630-278	RAL 7021	Struktur Pulvermaling	Stål	Side Panel, Screw Fixed
21630-231	RAL 7021	Struktur Pulvermaling	Stål	Side Panel, Screw Fixed

Katalognummer	Farvekode	Finish	Materiale	Type
21630-079	RAL 7021	Struktur Pulvermaling	Stål	Side Panel, Screw Fixed
21630-238	RAL 7021	Struktur Pulvermaling	Stål	Side Panel, Screw Fixed
21630-226	RAL 7021	Struktur Pulvermaling	Stål	Side Panel, Screw Fixed
21630-271	RAL 7021	Struktur Pulvermaling	Stål	Side Panel, Screw Fixed
21630-279	RAL 7021	Struktur Pulvermaling	Stål	Side Panel, Screw Fixed
21630-228	RAL 7021	Struktur Pulvermaling	Stål	Side Panel, Screw Fixed
21630-268	RAL 7021	Struktur Pulvermaling	Stål	Side Panel, Screw Fixed
21630-239	RAL 7021	Struktur Pulvermaling	Stål	Side Panel, Screw Fixed
21630-081	RAL 7021	Struktur Pulvermaling	Stål	Side Panel, Screw Fixed
21630-227	RAL 7021	Struktur Pulvermaling	Stål	Side Panel, Screw Fixed
21630-272	RAL 7021	Struktur Pulvermaling	Stål	Side Panel, Screw Fixed
21630-280	RAL 7021	Struktur Pulvermaling	Stål	Side Panel, Screw Fixed
21630-267	RAL 7021	Struktur Pulvermaling	Stål	Side Panel, Screw Fixed
21630-264	RAL 7021	Struktur Pulvermaling	Stål	Side Panel, Screw Fixed
21630-082	RAL 7021	Struktur Pulvermaling	Stål	Side Panel, Screw Fixed
21630-240	RAL 7021	Struktur Pulvermaling	Stål	Side Panel, Screw Fixed
21630-224	RAL 7021	Struktur Pulvermaling	Stål	Side Panel, Screw Fixed

Table 2/5

Katalognummer	Farvekode	Finish	Materiale	Type
21630-927	RAL 7021	Struktur Pulvermaling	Stål	Side Panel, Screw Fixed
21630-225	RAL 7021	Struktur Pulvermaling	Stål	Side Panel, Screw Fixed

Katalognummer	Farvekode	Finish	Materiale	Type
21630-043	RAL 7021	Struktur Pulvermaling	Stål	Side Panel, Screw Fixed
21630-223	RAL 7021	Struktur Pulvermaling	Stål	Side Panel, Screw Fixed
21630-241	RAL 7021	Struktur Pulvermaling	Stål	Side Panel, Screw Fixed
21630-263	RAL 7021	Struktur Pulvermaling	Stål	Side Panel, Screw Fixed
21630-274	RAL 7021	Struktur Pulvermaling	Stål	Side Panel, Screw Fixed
21630-270	RAL 7021	Struktur Pulvermaling	Stål	Side Panel, Screw Fixed
21630-249	RAL 7021	Struktur Pulvermaling	Stål	Side Panel, Screw Fixed
21630-047	RAL 7021	Struktur Pulvermaling	Stål	Side Panel, Screw Fixed
21630-230	RAL 7021	Struktur Pulvermaling	Stål	Side Panel, Screw Fixed
21630-048	RAL 7021	Struktur Pulvermaling	Stål	Side Panel, Screw Fixed
21630-243	RAL 7021	Struktur Pulvermaling	Stål	Side Panel, Screw Fixed
21630-273	RAL 7021	Struktur Pulvermaling	Stål	Side Panel, Screw Fixed
21630-229	RAL 7021	Struktur Pulvermaling	Stål	Side Panel, Screw Fixed
21630-045	RAL 7021	Struktur Pulvermaling	Stål	Side Panel, Screw Fixed
21630-242	RAL 7021	Struktur Pulvermaling	Stål	Side Panel, Screw Fixed
21630-233	RAL 7021	Struktur Pulvermaling	Stål	Side Panel, Screw Fixed
21630-044	RAL 7021	Struktur Pulvermaling	Stål	Side Panel, Screw Fixed
21630-467	RAL 7021	Struktur Pulvermaling	Stål	Side Panel, Screw Fixed

Table 3/5

Katalognummer	Farvekode	Finish	Materiale	Type
21630-250	RAL 7021	Struktur Pulvermaling	Stål	Side Panel, Screw Fixed

Katalognummer	Farvekode	Finish	Materiale	Type
21630-236	RAL 7021	Struktur Pulvermaling	Stål	Side Panel, Screw Fixed
21630-234	RAL 7021	Struktur Pulvermaling	Stål	Side Panel, Screw Fixed
21630-276	RAL 7021	Struktur Pulvermaling	Stål	Side Panel, Screw Fixed
21630-235	RAL 7021	Struktur Pulvermaling	Stål	Side Panel, Screw Fixed
21630-269	RAL 7021	Struktur Pulvermaling	Stål	Side Panel, Screw Fixed
21630-078	RAL 7021	Struktur Pulvermaling	Stål	Side Panel, Screw Fixed
21630-277	RAL 7021	Struktur Pulvermaling	Stål	Side Panel, Screw Fixed
21630-275	RAL 7021	Struktur Pulvermaling	Stål	Side Panel, Screw Fixed
21630-237	RAL 7021	Struktur Pulvermaling	Stål	Side Panel, Screw Fixed
21630-232	RAL 7021	Struktur Pulvermaling	Stål	Side Panel, Screw Fixed
21630-262	RAL 7021	Struktur Pulvermaling	Stål	Side Panel, Screw Fixed
21630-933	RAL 7021	Struktur Pulvermaling	Stål	Side Panel, Screw Fixed
21630-283	RAL 7021	Struktur Pulvermaling	Stål	Side Panel, Screw Fixed
21630-478	RAL 7021	Struktur Pulvermaling	Stål	Side Panel, Screw Fixed
21630-465	RAL 7021	Struktur Pulvermaling	Stål	Side Panel, Screw Fixed
21630-477	RAL 7021	Struktur Pulvermaling	Stål	Side Panel, Screw Fixed
21630-246	RAL 7021	Struktur Pulvermaling	Stål	Side Panel, Screw Fixed
21630-077	RAL 7021	Struktur Pulvermaling	Stål	Side Panel, Screw Fixed
21630-284	RAL 7021	Struktur Pulvermaling	Stål	Side Panel, Screw Fixed

Table 4/5

Katalognummer	Farvekode	Finish	Materiale	Type
---------------	-----------	--------	-----------	------

21630-931	RAL 7021	Struktur Pulvermaling	Stål	Side Panel, Screw Fixed
21630-476	RAL 7021	Struktur Pulvermaling	Stål	Side Panel, Screw Fixed
21630-930	RAL 7021	Struktur Pulvermaling	Stål	Side Panel, Screw Fixed
21630-475	RAL 7021	Struktur Pulvermaling	Stål	Side Panel, Screw Fixed
21630-247	RAL 7021	Struktur Pulvermaling	Stål	Side Panel, Screw Fixed
21630-471	RAL 7021	Struktur Pulvermaling	Stål	Side Panel, Screw Fixed
21630-474	RAL 7021	Struktur Pulvermaling	Stål	Side Panel, Screw Fixed
21630-046	RAL 7021	Struktur Pulvermaling	Stål	Side Panel, Screw Fixed
21630-932	RAL 7021	Struktur Pulvermaling	Stål	Side Panel, Screw Fixed
21630-473	RAL 7021	Struktur Pulvermaling	Stål	Side Panel, Screw Fixed
21630-248	RAL 7021	Struktur Pulvermaling	Stål	Side Panel, Screw Fixed
21630-472	RAL 7021	Struktur Pulvermaling	Stål	Side Panel, Screw Fixed
21630-221	RAL 7021	Struktur Pulvermaling	Stål	Side Panel, Screw Fixed
21630-469	RAL 7021	Struktur Pulvermaling	Stål	Side Panel, Screw Fixed
21630-928	RAL 7021	Struktur Pulvermaling	Stål	Side Panel, Screw Fixed
21630-050	RAL 7021	Struktur Pulvermaling	Stål	Side Panel, Screw Fixed
21630-468	RAL 7021	Struktur Pulvermaling	Stål	Side Panel, Screw Fixed
21630-261	RAL 7021	Struktur Pulvermaling	Stål	Side Panel, Screw Fixed
21630-265	RAL 7021	Struktur Pulvermaling	Stål	Side Panel, Screw Fixed
21630-934	RAL 7021	Struktur Pulvermaling	Stål	Side Panel, Screw Fixed

Table 5/5

Katalognummer	Farvekode	Finish	Materiale	Type
---------------	-----------	--------	-----------	------

21630-281	RAL 7021	Struktur Pulvermaling	Stål	Side Panel, Screw Fixed
21630-051	RAL 7021	Struktur Pulvermaling	Stål	Side Panel, Screw Fixed
21630-244	RAL 7021	Struktur Pulvermaling	Stål	Side Panel, Screw Fixed
21630-049	RAL 7021	Struktur Pulvermaling	Stål	Side Panel, Screw Fixed
21630-222	RAL 7021	Struktur Pulvermaling	Stål	Side Panel, Screw Fixed
21630-466	RAL 7021	Struktur Pulvermaling	Stål	Side Panel, Screw Fixed
21630-080	RAL 7021	Struktur Pulvermaling	Stål	Side Panel, Screw Fixed
21630-929	RAL 7021	Struktur Pulvermaling	Stål	Side Panel, Screw Fixed
21630-282	RAL 7021	Struktur Pulvermaling	Stål	Side Panel, Screw Fixed
21630-480	RAL 7021	Struktur Pulvermaling	Stål	Side Panel, Screw Fixed
21630-245	RAL 7021	Struktur Pulvermaling	Stål	Side Panel, Screw Fixed
21630-479	RAL 7021	Struktur Pulvermaling	Stål	Side Panel, Screw Fixed
21630-470	RAL 7021	Struktur Pulvermaling	Stål	Side Panel, Screw Fixed

YDERLIGERE PRODUKTOPLYSNINGER

Please purchase the grounding kit separately.

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE