


Varistar CP Deco Frame Adapter Bracket



Adapter Brackets are helpful in assembling slide rails and shelves for a nopen frame Varistar cabinet with deco frame.

CERTIFICERINGER



FUNKTIONER

For assembling slide rails and shelves in Varistar Deco

SPECIFIKATIONER

Product Type: Bracket
Materiale: Stål

Table 1/2

Katalognummer	Rack Height	Højde	Pakke mængde	Farve	Farvekode	Finish
23130-231	29U	1400mm	2	Light Grey	RAL 7035	Struktur Pulvermaling
23130-223	38U	1800mm	2	Black Grey	RAL 7021	Struktur Pulvermaling
23130-224	42U	2000mm	2	Black Grey	RAL 7021	Struktur Pulvermaling
23130-225	47U	2200mm	2	Black Grey	RAL 7021	Struktur Pulvermaling
23130-222	33U	1600mm	2	Black Grey	RAL 7021	Struktur Pulvermaling
23130-230	24U	1200mm	2	Light Grey	RAL 7035	Struktur Pulvermaling
23130-232	33U	1600mm	2	Light Grey	RAL 7035	Struktur Pulvermaling
23130-221	29U	1400mm	2	Black Grey	RAL 7021	Struktur Pulvermaling
23130-233	38U	1800mm	2	Light Grey	RAL 7035	Struktur Pulvermaling
23130-234	42U	2000mm	2	Light Grey	RAL 7035	Struktur Pulvermaling
23130-220	24U	1200mm	2	Black Grey	RAL 7021	Struktur Pulvermaling
23130-235	47U	2200mm	2	Light Grey	RAL 7035	Struktur Pulvermaling

Table 2/2

Katalognummer	Type	Bredde	Works With
23130-231	Deco Frame Bracket	600mm	Cabinet
23130-223	Deco Frame Bracket	600mm	Cabinet, Varistar CP
23130-224	Deco Frame Bracket	600mm	Cabinet, Varistar CP
23130-225	Deco Frame Bracket	600mm	Cabinet, Varistar CP
23130-222	Deco Frame Bracket	600mm	Cabinet, Varistar CP
23130-230	Deco Frame Bracket	600mm	Cabinet
23130-232	Deco Frame Bracket	600mm	Cabinet
23130-221	Deco Frame Bracket	600mm	Cabinet, Varistar CP
23130-233	Deco Frame Bracket	600mm	Cabinet
23130-234	Deco Frame Bracket	600mm	Cabinet
23130-220	Bracket	600mm	Varistar, Varistar CP

Katalognummer	Type	Bredde	Works With
23130-235	Deco Frame Bracket	600mm	Cabinet

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE