



Modulschiene vorne, Typ H-KD, schwer, kurze Lippe, 63 TE

KATALOGNUMMER

34560-263



Combinations of horizontal rails and side panels

“+” = can be combined, “-” = combination not recommended

Support # 1		-	Technical for Acoustic Protection	Technical for Acoustic Protection	Technical for Acoustic Protection	Technical for Acoustic Protection
Support # 2		+	Technical for Acoustic Protection	Technical for Acoustic Protection	Technical for Acoustic Protection	Technical for Acoustic Protection
Support # 3		+	Technical for Acoustic Protection	Technical for Acoustic Protection	Technical for Acoustic Protection	Technical for Acoustic Protection
Horizontal rail		+	Technical for Acoustic Protection	Technical for Acoustic Protection	Technical for Acoustic Protection	Technical for Acoustic Protection
Side panel		+	Technical for Acoustic Protection	Technical for Acoustic Protection	Technical for Acoustic Protection	Technical for Acoustic Protection
		+	Technical for Acoustic Protection	Technical for Acoustic Protection	Technical for Acoustic Protection	Technical for Acoustic Protection
		+	Technical for Acoustic Protection	Technical for Acoustic Protection	Technical for Acoustic Protection	Technical for Acoustic Protection
		+	Technical for Acoustic Protection	Technical for Acoustic Protection	Technical for Acoustic Protection	Technical for Acoustic Protection
		+	Technical for Acoustic Protection	Technical for Acoustic Protection	Technical for Acoustic Protection	Technical for Acoustic Protection

Only panels shown

Modulschiene aus Aluminiumprofil vom Typ H-KD (H-KD = schwer, kurze Lippe) mit eloxierter Oberfläche und leitfähiger Kontaktfläche. Ohne Bedruckung (TE Markierung). Geeignet für RatiopacPRO/-AIR und EuropacPRO/-rugged)

ZERTIFIZIERUNGEN



MERKMALE

Einbau im Baugruppenträger kann oben und unten erfolgen

Kurze Lippe (H-KD)

Aluminiumprofil, Oberfläche eloxiert, Kontaktfläche leitfähig

PRODUKTMERKMALE

Breite Gestell: 63HP

Anzahl Verpackungen: 1

Oberfläche: Eloxiert

Länge: 325.12mm

Material: Aluminium

Produktfamilie: EuropacPRO; RatiopacPRO; RatiopacPRO AIR; CompacPRO; PropacPRO

Produkttyp: Modulschiene

Typ: Schwer, KD

Passt zu: Baugruppenträger; Gehäuse

Net Weight: 0.127kg

ZUSÄTZLICHE PRODUKTDDETAILS

Die Lieferung erfolgt in Lieferlosgrößen. Die Preise gelten pro einzelnen Artikel.

Bitte beachten Sie, dass Lieferungen nur in den jeweils angegebenen LLG (Lieferlosgrößen), LLG z. B. 5 Stück, 10 Stück, 50 Stück usw.) möglich sind. Davon abweichende Bestellmengen (z. B. 2 Stück) werden auf die nächst mögliche lieferbare Menge = Lieferlosgröße (LLG) abgeändert.

WARNUNG

nVent-Produkte müssen in Übereinstimmung mit den Produktinformationsblättern und dem Schulungsmaterial von nVent installiert und verwendet werden. Informationsblätter sind verfügbar unter www.nVent.com sowie bei Ihrem nVent-Kundendienstvertreter. Unsachgemäße Installation, Missbrauch, Fehlanwendung oder andere Handlungen im Widerspruch zu den Anweisungen und Warnungen von nVent können zu Fehlfunktionen, Anlagenschäden, schwerer Körperverletzung sowie zum Tod führen und/oder haben die Annullierung der Garantie zur Folge.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Unser starkes markenportfolio:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE