

# Varistar CP Base/Plinth

## Data Solutions

A plinth allows functional storage of excess cable assemblies and protects the bottom part of the cabinet against rodents.



### FEATURES

2 support profiles, for front and rear

Static load-carrying capacity 1000 kg

### SPECIFICATIONS

**Product Type:** Cabinet/Rack Base

**Material:** Steel

Table 1/2

| Catalog Number | Height | Width | Package Quantity | Color      | Color Code | Depth |
|----------------|--------|-------|------------------|------------|------------|-------|
| 24630-037      | 200mm  | 800mm | 1                | Black Grey | RAL 7021   |       |
| 24630-034      | 100mm  | 600mm | 1                | Black Grey | RAL 7021   | 600mm |
| 24630-066      | 200mm  | 600mm | 1                | Black Grey | RAL 7021   |       |
| 24630-035      | 100mm  | 800mm | 1                | Black Grey | RAL 7021   |       |
| 24630-065      | 100mm  | 800mm | 1                | Black Grey | RAL 7021   |       |
| 24630-064      | 100mm  | 600mm | 1                | Black Grey | RAL 7021   |       |
| 24630-036      | 200mm  | 600mm | 1                | Black Grey | RAL 7021   |       |
| 24630-067      | 200mm  | 800mm | 1                | Black Grey | RAL 7021   |       |

Table 2/2

| Catalog Number | Finish        | Type                    |
|----------------|---------------|-------------------------|
| 24630-037      | Powder Coated | Base Plinth, Perforated |
| 24630-034      | Powder Coated | Base Plinth, Perforated |
| 24630-066      | Powder Coated | Base Plinth, Plain      |
| 24630-035      | Powder Coated | Base Plinth, Perforated |
| 24630-065      | Powder Coated | Base Plinth, Plain      |
| 24630-064      | Powder Coated | Base Plinth, Plain      |
| 24630-036      | Powder Coated | Base Plinth, Perforated |
| 24630-067      | Powder Coated | Base Plinth, Plain      |

## ADDITIONAL PRODUCT DETAILS

---

Please order side trims separately.

Cannot be used in conjunction with castors

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**