

DC Fan

Axial fan, 119 mm, with DC input. Replacement part for 1 U fan trays.



CERTIFICATIONS



FEATURES

Axial 119 mm DC fan, with plug for connection cable

SPECIFICATIONS

Table 1/2

Catalog Number	Works With	Width	Length	Height	Voltage DC	Airflow
60713-600	19" Fan Trays	119mm	119mm	32mm	12V	140m ³ /h
20713-242	19" Fan Trays	119mm	119mm	38mm	48V	184m ³ /h
20713-241	19" Fan Trays	119mm	119mm	38mm	12V	184m ³ /h
20713-240	19" Fan Trays	119mm	119mm	38mm	24V	184m ³ /h
20713-172	19" Fan Trays	119mm	119mm	25.5mm	24V	171m ³ /h

Table 2/2

Catalog Number	Noise Level	Power	Max Static Pressure	Ambient Temperature	Package Quantity
60713-600	39dB(A)	8W	46Pa	70°C	1
20713-242	42dB(A)	8W	68Pa	70°C	1

Catalog Number	Noise Level	Power	Max Static Pressure	Ambient Temperature	Package Quantity
20713-241	42dB(A)	8W	68Pa	70°C	1
20713-240	42dB(A)	8W	68Pa	70°C	1
20713-172	50.5dB(A)	7W	50.5Pa	70°C	1

ADDITIONAL PRODUCT DETAILS

Please order connection cable and protective grille separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE