

# Countersunk Screw, Torx

Screw for cases, systems, and subracks to secure several accessories.



## CERTIFICATIONS



## FEATURES

For screwing of Subrack or Case accessories

## SPECIFICATIONS

- Product Family:** EuropacPRO; RatiopacPRO; RatiopacPRO AIR; CompacPRO; PropacPRO; MultipacPRO
- Type:** Countersunk Screw
- Product Type:** Screw

| Table 1/2      |        |          |               |                  |             |                          |
|----------------|--------|----------|---------------|------------------|-------------|--------------------------|
| Catalog Number | Length | Material | Finish        | Package Quantity | Thread Size | Works With               |
| 24571-373      | 8mm    | Steel    | Nickel Plated | 100              | M4          | RatiopacPRO              |
| 24560-146      | 5mm    | Steel    | Nickel Plated | 100              | M2.5        | Subracks, Cases, Chassis |

| Table 2/2      |        |                |
|----------------|--------|----------------|
| Catalog Number | Torque | Certifications |
| 24571-373      | 2.4N·m |                |

| Catalog Number | Torque | Certifications |
|----------------|--------|----------------|
| 24560-146      |        | RoHS           |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**