

APY External Horizontal Wall Bracket



FEATURES

Side mount saddle support for C-Profiles and strut

Complete with fixings

SPECIFICATIONS

Table 1/2

| Catalog Number | Article Number | Material | Finish | Channel Type | Strut Type | Height (H) |
|----------------|----------------|---------------------------------------|-------------------|--------------|-----------------------------------|------------|
| APYSTRUTS6 | 584840 | Stainless Steel 316 (EN 1.4401) | | | A (41 x 41 mm), C (21 x 41 mm) | 50 mm |
| APYE23EG | 584740 | Steel | Electrogalvanized | E2L, E2, E3 | | 40 mm |
| APYE4STRUTEG | 584751 | Steel | Electrogalvanized | E4 | A (41 x 41 mm), C (21 x 41 mm) | 50 mm |
| APYE01EG | 584758 | Steel | Electrogalvanized | E0L, E0, E1 | | 40 mm |

Table 2/2

| Catalog Number | Article Number | Width (W) | Thickness (T) | A | B | C |
|----------------|----------------|-----------|---------------|-------|-------|-------|
| APYSTRUTS6 | 584840 | 144 mm | 5 mm | 43 mm | 12 mm | 19 mm |
| APYE23EG | 584740 | 124 mm | 5 mm | 36 mm | 12 mm | 19 mm |
| APYE4STRUTEG | 584751 | 144 mm | 5 mm | 43 mm | 12 mm | 19 mm |

| Catalog Number | Article Number | Width (W) | Thickness (T) | A | B | C |
|----------------|----------------|-----------|---------------|-------|-------|-------|
| APYE01EG | 584758 | 124 mm | 5 mm | 31 mm | 12 mm | 19 mm |

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

