

LED Lights for Cabinets

Data Solutions



The enclosure light provides a compact and flexible solution, and offers fast, easy assembly and installation. For mounting flexibility, the LED light can be fastened to the enclosure with screws or quickly attached to any flat steel surfaces with optional magnetic kits. A motion sensor is also available.

CERTIFICATIONS



FEATURES

Power cable for LED light mounting into cabinet

Lights can be easily mounted vertically or horizontally

Simple through-wiring based on a plug-and-play system

SPECIFICATIONS

Product Type: Light

Table 1/2

| Catalog Number | Accessory Type | Protection Rating | Package Quantity | Color | Finish | Type |
|----------------|----------------|-------------------|------------------|-------|--------------|-------------------------------|
| 57274 | Lights | IP20 | 1 | Black | Smooth Matte | Cabinet Light, Terminal Block |
| 57275 | Lights | IP20 | 2 | | Smooth Matte | Cabinet Light, Magnet |
| 60130-114 | Lights | IP20 | 1 | | Smooth | Connection Cable |

| Catalog Number | Accessory Type | Protection Rating | Package Quantity | Color | Finish | Type |
|----------------|----------------|-------------------|------------------|-------|--------------|------------------|
| 57265 | Lights | IP20 | 1 | Black | Smooth Matte | Cabinet Light |
| 57272 | Lights | IP20 | 1 | Black | Smooth | Connection Cable |
| 57273 | Lights | IP20 | 1 | Black | Smooth | Connection Cable |

Table 2/2

| Catalog Number | Connection Type | Light Output | Rated Current | Weight | Certifications |
|----------------|-------------------------------|--------------|---------------|---------|----------------|
| 57274 | Infeed, Trough-Wiring, 2-Pole | | 16A | 0.07kg | RoHS |
| 57275 | | | | 0.08kg | RoHS |
| 60130-114 | Infeed, Trough-Wiring, 2-Pole | | 10A | 0.083kg | RoHS, EAC |
| 57265 | Infeed, Trough-Wiring, 2-Pole | 550lm | | 0.24kg | CE, RoHS |
| 57272 | Infeed, Trough-Wiring, 2-Pole | | 10A | 0.3kg | RoHS |
| 57273 | Infeed, Trough-Wiring, 2-Pole | | 10A | 0.3kg | RoHS |

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE