

# Rubber Mount



The Vibration Isolation Mount line from nVent CADDY is used to minimize vibrations produced by supported systems such as mechanical equipment, pumps, ductwork, piping, and in-line, exhaust and cabinet fans.

## FEATURES

Used to support HVAC equipment, air conditioning units, compressors, pumps, motors and fan pumps

Color coded for accurate selection and easy field verification

Rubber surface provides anti-skid properties

## SPECIFICATIONS

Table 1/1

Catalog Number	Article Number	Length	Width	Height	Ultimate Static Load
VIBRMA100	801419	44.45mm	79.375mm	31.75mm	445N
VIBRMA060	801418	44.45mm	79.375mm	31.75mm	267N
VIBRMA015	801416	44.45mm	79.375mm	31.75mm	67N
VIBRMA030	801417	44.45mm	79.375mm	31.75mm	134N
VIBRMB150	801421	60.33mm	98.425mm	44.45mm	668N
VIBRMB200	801422	60.33mm	98.425mm	44.45mm	890N
VIBRMB300	801423	60.33mm	98.425mm	44.45mm	1335N
VIBRMB120	801420	60.33mm	98.425mm	44.45mm	534N
VIBRMC200	801424	60.33mm	101.6mm	50.8mm	890N
VIBRMC300	801425	60.33mm	101.6mm	50.8mm	1335N
VIBRMC500	801427	60.33mm	101.6mm	50.8mm	2224N
VIBRMC400	801426	60.33mm	101.6mm	50.8mm	1780N
VIBRMD1000	801429	60.33mm	149.225mm	88.9mm	4448N

Catalog Number	Article Number	Length	Width	Height	Ultimate Static Load
VIBRMD1500	801430	60.33mm	149.225mm	88.9mm	6672N
VIBRMD750	801428	60.33mm	149.225mm	88.9mm	3336N
VIBRMD2200	801431	60.33mm	149.225mm	88.9mm	9786N

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE

