

# 19" Cable Ducting

19" unit for easy and effective cable management (cable ducting).



## CERTIFICATIONS



## FEATURES

19" Front panel for cable ducting

## SPECIFICATIONS

- Accessory Type:** Front panel
- Product Type:** Front Panel
- Material:** Steel

Table 1/3

Catalog Number	Rack Height	Mounting	Package Quantity	Front Finish	Rear Finish	Color Code
20118-734	1U	Screw-on Front	1	Painted	Painted	RAL 7035
20118-767	1U	Screw-on Front	1	Painted	Painted	RAL 7021
20118-736	2U	Screw-on Front	1	Painted	Painted	RAL 7035
20118-768	2U	Screw-on Front	1	Anodized	Conductive	RAL 7021

Table 2/3

Catalog Number	Depth	EMC Shielding	Finish	Height	Rack Width	Type
20118-734	1.5mm	No	Powder Coated	43.6mm	95HP	19" Front Panel
20118-767	1.5mm	No	Powder Coated	43.6mm	95HP	19" Front Panel
20118-736	1.5mm	No	Powder Coated	88.1mm	95HP	19" Front Panel
20118-768	1.5mm	No	Powder Coated	88.1mm	95HP	19" Front Panel

Table 3/3

Catalog Number	Width
20118-734	483mm
20118-767	483mm
20118-736	483mm
20118-768	483mm

## ADDITIONAL PRODUCT DETAILS

Please order 19" assembly kit separately.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**