

# Socket Strip, UTE, With Wieland® Input



Modular, compact PDU with many function elements. Using a 1 U by 1 U aluminum chassis the PDU can easily be integrated in a rack. The Wieland connector allows easy combination with different power input cords.

## CERTIFICATIONS



## FEATURES

Input via Wieland® GST 18 plug

Socket strips can be rotated through all four directions (in 90° increments) during fitting

Output via UTE sockets

Horizontal or vertical mounting

Installation height 1 U

In accordance with NFC 61-303

## SPECIFICATIONS

- Length:** 438.5mm
- Material:** Aluminum; Polyamide
- Product Type:** Socket Strip

Table 1/2

Catalog Number	Socket Type	Socket Quantity	Switched Outlets	Voltage AC	Function	Package Quantity
60110-357	UTE	6	No	230V	Overcurrent Protection	1

Catalog Number	Socket Type	Socket Quantity	Switched Outlets	Voltage AC	Function	Package Quantity
60110-356	UTE	6	No	230V	Overcurrent Protection	1
60110-346	UTE	8	No	230V		1
60110-355	UTE	6	No	230V	Overcurrent Protection	1
60110-348	UTE	8	No	230V		1
60110-347	UTE	8	No	230V		1

Table 2/2

Catalog Number	Color	Depth	Finish
60110-357	Red	44mm	Anodized
60110-356	Black	44mm	Anodized
60110-346	White	44mm	Anodized
60110-355	White	44mm	Anodized
60110-348	Red	44mm	Anodized
60110-347	Black	44mm	Anodized

## ADDITIONAL PRODUCT DETAILS

---

Please order mounting bracket for vertical mounting separately.

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations

+1.763.422.2661

Chat with us:

[nvent.com/schroff](https://nvent.com/schroff)

### Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

[nvent.com/schroff](https://nvent.com/schroff)

### Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

[nvent.com/schroff](https://nvent.com/schroff)

### Middle East & India

Dubai, United Arab

Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

[nvent.com/schroff](https://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY**

**ERICO**

**HOFFMAN**

**ILSCO**

**SCHROFF**

**TRACHTE**