

# Mains Cable



nVent SCHROFF Mains cable provides practical, universal fastening with variable attachment facilities. They are general in nature and fit in to different applications like Fans, cabinet lights, etc., Industrial PC connections, Uninterruptible power supplies, Systems.

## CERTIFICATIONS



## FEATURES

Applications: Fans, cabinet lights, Industrial PC connections, Uninterruptible power supplies and Systems

## SPECIFICATIONS

**Product Type:** Cable

Table 1/2

Catalog Number	Input Connector	Output Connector	Length	Package Quantity	Color	Connector Type
62150-191	SCHUKO / UTE	IEC C13	2500mm	1	Black	Straight
60704-020	SCHUKO / UTE	IEC C13	2500mm	1	Grey	Angled
60103-131	SCHUKO / UTE	IEC C13	2500mm	1	Grey	Straight
60110-361	IEC C14	IEC C13	1000mm	1	Black	Straight
60197-053	IEC C14	IEC C13	2500mm	1	Black	Straight
60110-360	IEC C14	IEC C13	500mm	1	Black	Straight
60103-137	BS = British Standard	IEC C13	2500mm	1	Black	Straight

Catalog Number	Input Connector	Output Connector	Length	Package Quantity	Color	Connector Type
60103-141	US = US Standard	IEC C13	2500mm	1	Black	Straight

Table 2/2

Catalog Number	Material
62150-191	PVC
60704-020	PVC
60103-131	PVC
60110-361	PVC
60197-053	PVC
60110-360	PVC
60103-137	PVC
60103-141	PVC

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**