

Cable Entry Gland Plate Rectangular, CEPH



CEPH cable entry provides a very flat, space-saving professional cable entry with a very tight seal. The special shape of the membrane cone grommet helps ensure optimal strain relief.

INDUSTRY STANDARDS

UL 508A Component Recognized; Type 1, 12, 4X (indoor only); File No. E61997

UL94 V-0 Flammability

NEMA Type 1, 12, 4X (indoor only)

CE

IP66

FEATURES

Description: Fast, cost-effective cable entry with a tight seal for incoming cables and/or pneumatic conduits inside an enclosure. Can be affixed with screws or the built-in snap-in system that works for wall thicknesses of 1.5 to 2.5 mm.

Finish: Black

Flammability: UL94 V-0

Material: Polyamide 6.6 / TPE

Pack quantity: 1 pc

Protection: IP66, NEMA 1, 4x, 12 (Indoor use only)

Temperature resistance: -40°C to +90°C

SPECIFICATIONS

Table 1/1

| Catalog Number | Article Number | Cable Entry Quantity | Cable Entry | Cutout Size | Height | Width |
|----------------|----------------|----------------------|--|-------------|--------|---------|
| CEPH2124 | 58313 | 21 | (1) 3.2 - 6.3 mm, (14) 4.0 - 7.5 mm, (4) 5.5 - 10.5 mm, (2) 8.0 - 12.5 mm | 36 x 112mm | 58mm | 149.6mm |
| CEPH1624 | 58307 | 16 | (2) 3.2 - 6.3 mm, (9) 4.0 - 7.5 mm, (1) 5.5 - 10.5 mm, (1) 8.0 - 12.5 mm, (3) 12.0 - 16.2 mm | 36 x 112mm | 58mm | 149.6mm |
| CEPH16124 | 58308 | 16 | (8) 3.2 - 5.5 mm, (6) 5.0 - 8.5 mm, (2) 9.5 - 14.5 mm | 36 x 112mm | 58mm | 149.6mm |
| CEPH3224 | 58314 | 32 | (32) 3.2 - 6.3 mm | 36 x 112mm | 58mm | 149.6mm |
| CEPH2024 | 58309 | 20 | (12) 3.2 - 6.3 mm, (8) 5.5 - 10.5 mm | 36 x 112mm | 58mm | 149.6mm |
| CEPH1324 | 58306 | 13 | (10) 3.2 - 6.3 mm, (3) 16.0 - 20.5 mm | 36 x 112mm | 58mm | 149.6mm |

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE