

ProLine Solid Sides



Solid Sides close the open sides of an enclosure frame and attach to the enclosure frame with semi-flush screws. Hangers are included for easy alignment of screws. Sides have two grounding studs and a foam-in-place gasket. Mounting hardware is included. Solid Sides are not suitable as barriers between joined enclosures.

FEATURES

Solid Sides are finished with paint over plated surfaces

SPECIFICATIONS

Table 1/3

| Catalog Number | Article Number | Material | Finish | Color | Color Code | Thickness |
|----------------|----------------|---------------------|---------|------------|------------|-----------|
| PSS165HF2 | 11499 | Mild Steel | | Light Gray | RAL 7035 | 1.52mm |
| PSS186 | 96220 | Mild Steel | | Light Gray | RAL 7035 | 1.52mm |
| PSS145HF2 | 11459 | Mild Steel | | Light Gray | RAL 7035 | 1.52mm |
| PSS185 | 96210 | Mild Steel | | Light Gray | RAL 7035 | 1.52mm |
| PSS146HF2 | 11469 | Mild Steel | | Light Gray | RAL 7035 | 1.52mm |
| PSS168 | 96180 | Mild Steel | | Light Gray | RAL 7035 | 1.52mm |
| PSS164HF2 | 11489 | Mild Steel | | Light Gray | RAL 7035 | 1.52mm |
| PSS165 | 96160 | Mild Steel | | Light Gray | RAL 7035 | 1.52mm |
| PSS168SS | 31739 | Stainless Steel 304 | Brushed | | | 1.52mm |
| PSS125 | 30438 | Mild Steel | | Light Gray | RAL 7035 | 1.52mm |
| PSS166SS | 31729 | Stainless Steel 304 | Brushed | | | 1.52mm |
| PSS184HF2 | 11539 | Mild Steel | | Light Gray | RAL 7035 | 1.52mm |
| PSS166 | 96170 | Mild Steel | | Light Gray | RAL 7035 | 1.52mm |
| PSS186HF2 | 11559 | Mild Steel | | Light Gray | RAL 7035 | 1.52mm |
| PSS188HF2 | 11569 | Mild Steel | | Light Gray | RAL 7035 | 1.52mm |
| PSS164 | 96150 | Mild Steel | | Light Gray | RAL 7035 | 1.52mm |
| PSS204HF2 | 11589 | Mild Steel | | Light Gray | RAL 7035 | 1.52mm |
| PSS206HF2 | 11609 | Mild Steel | | Light Gray | RAL 7035 | 1.52mm |
| PSS228 | 96310 | Mild Steel | | Light Gray | RAL 7035 | 1.52mm |
| PSS208 | 96280 | Mild Steel | | Light Gray | RAL 7035 | 1.52mm |

Table 2/3

| Catalog Number | Article Number | Material | Finish | Color | Color Code | Thickness |
|----------------|----------------|---------------------|---------|------------|------------|-----------|
| PSS208SS | 31779 | Stainless Steel 304 | Brushed | | | 1.52mm |
| PSS206SS | 31769 | Stainless Steel 304 | Brushed | | | 1.52mm |
| PSS204 | 96250 | Mild Steel | | Light Gray | RAL 7035 | 1.52mm |
| PSS206 | 96270 | Mild Steel | | Light Gray | RAL 7035 | 1.52mm |
| PSS225 | 90730 | Mild Steel | | Light Gray | RAL 7035 | 1.52mm |
| PSS205 | 96260 | Mild Steel | | Light Gray | RAL 7035 | 1.52mm |
| PSS226 | 96300 | Mild Steel | | Light Gray | RAL 7035 | 1.52mm |
| PSS148HF2 | 11479 | Mild Steel | | Light Gray | RAL 7035 | 1.52mm |
| PSS184 | 96200 | Mild Steel | | Light Gray | RAL 7035 | 1.52mm |

| Catalog Number | Article Number | Material | Finish | Color | Color Code | Thickness |
|----------------|----------------|---------------------|---------|------------|------------|-----------|
| PSS228SS | 31799 | Stainless Steel 304 | Brushed | | | 1.52mm |
| PSS188 | 96230 | Mild Steel | | Light Gray | RAL 7035 | 1.52mm |
| PSS76SS | 31699 | Stainless Steel 304 | Brushed | | | 1.52mm |
| PSS188SS | 31759 | Stainless Steel 304 | Brushed | | | 1.52mm |
| PSS76 | 96110 | Mild Steel | | Light Gray | RAL 7035 | 1.52mm |
| PSS186SS | 31749 | Stainless Steel 304 | Brushed | | | 1.52mm |
| PSS145 | 96120 | Mild Steel | | Light Gray | RAL 7035 | 1.52mm |
| PSS225HF2 | 16959 | Mild Steel | | Light Gray | RAL 7035 | 1.52mm |
| PSS148 | 96140 | Mild Steel | | Light Gray | RAL 7035 | 1.52mm |
| PSS228HF2 | 11649 | Mild Steel | | Light Gray | RAL 7035 | 1.52mm |
| PSS148SS | 31719 | Stainless Steel 304 | Brushed | | | 1.52mm |

Table 3/3

| Catalog Number | Article Number | Material | Finish | Color | Color Code | Thickness |
|----------------|----------------|---------------------|---------|------------|------------|-----------|
| PSS146 | 96130 | Mild Steel | | Light Gray | RAL 7035 | 1.52mm |
| PSS146SS | 31709 | Stainless Steel 304 | Brushed | | | 1.52mm |
| PSS208HF2 | 11619 | Mild Steel | | Light Gray | RAL 7035 | 1.52mm |
| PSS76HF2 | 11449 | Mild Steel | | Light Gray | RAL 7035 | 1.52mm |
| PSS209 | 96290 | Mild Steel | | Light Gray | RAL 7035 | 1.9mm |
| PSS229HF2 | 11659 | Mild Steel | | Light Gray | RAL 7035 | 1.9mm |
| PSS209HF2 | 11629 | Mild Steel | | Light Gray | RAL 7035 | 1.9mm |
| PSS229 | 96320 | Mild Steel | | Light Gray | RAL 7035 | 1.9mm |

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE