


# ProTek Rack Angles

## Data Solutions



The ProTek Rack Angles support 19in rack equipment in the single- and double-hinged ProTek product. The square- and tapped-hole rack angles support EIA spaced IT equipment that is to be mounted within a ProTek cabinet.

### FEATURES

The ProTek Rack Angles support 19in rack equipment in the single- and double-hinged ProTek product

The square- and tapped-hole rack angles support EIA spaced IT equipment that is to be mounted within a ProTek cabinet

### SPECIFICATIONS

Table 1/2

| Catalog Number | Article Number | Height | Material   | Finish      | Thickness | Hole Type |
|----------------|----------------|--------|------------|-------------|-----------|-----------|
| PTRA24T        | 23772          | 533mm  | Mild Steel | Zinc Plated | 2.66mm    | Tapped    |
| PTRA60T        | 23778          | 1422mm | Mild Steel | Zinc Plated | 2.66mm    | Tapped    |
| PTRA16S        | 23771          | 356mm  | Mild Steel | Zinc Plated | 2.66mm    | Square    |
| PTRA24S        | 23773          | 533mm  | Mild Steel | Zinc Plated | 2.66mm    | Square    |
| PTRA48T        | 23776          | 1156mm | Mild Steel | Zinc Plated | 2.66mm    | Tapped    |
| PTRA36T        | 23774          | 845mm  | Mild Steel | Zinc Plated | 2.66mm    | Tapped    |
| PTRA48S        | 23777          | 1156mm | Mild Steel | Zinc Plated | 2.66mm    | Square    |
| PTRA16T        | 23768          | 356mm  | Mild Steel | Zinc Plated | 2.66mm    | Tapped    |
| PTRA60S        | 23781          | 1422mm | Mild Steel | Zinc Plated | 2.66mm    | Square    |
| PTRA36S        | 23775          | 845mm  | Mild Steel | Zinc Plated | 2.66mm    | Square    |

Table 2/2

| Catalog Number | Article Number | Rack Units |
|----------------|----------------|------------|
| PTRA24T        | 23772          | 12U        |
| PTRA60T        | 23778          | 32U        |
| PTRA16S        | 23771          | 8U         |
| PTRA24S        | 23773          | 12U        |
| PTRA48T        | 23776          | 26U        |
| PTRA36T        | 23774          | 19U        |
| PTRA48S        | 23777          | 26U        |
| PTRA16T        | 23768          | 8U         |
| PTRA60S        | 23781          | 32U        |
| PTRA36S        | 23775          | 19U        |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**