

# Panhead Screw, Torx

Panhead screws.



## CERTIFICATIONS



## FEATURES

Panhead screw

## SPECIFICATIONS

**Type:** Panhead Screw  
**Product Type:** Screw  
**Material:** Steel

Table 1/2

Catalog Number	Length	Finish	Package Quantity	Thread Size	Product Family	Works With
24560-148	10mm	Nickel Plated	100	M2.5		Backplanes, Test Adapters
24560-147	7mm	Nickel Plated	100	M2.5	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO	Front Panels, Eurorack, Novastar, Varistar, Varistar CP

Catalog Number	Length	Finish	Package Quantity	Thread Size	Product Family	Works With
24560-161	12mm	Nickel Plated	100	M2.5		Backplanes, Test Adapters
24560-135	6mm	Zinc Plated	100	M4	EuropacPRO	Subracks
24571-372	10mm	Zinc Plated	100	M4	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO	Front Panels, Eurorack, Novastar, Varistar, Varistar CP
24571-371	14mm	Zinc Plated	100	M4	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO	Front Panels, Eurorack, Novastar, Varistar, Varistar CP
24560-178	6mm	Nickel Plated	100	M2.5	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO	Front Panels, Eurorack, Novastar, Varistar, Varistar CP
24560-162	14mm	Nickel Plated	100	M2.5		Backplanes, Test Adapters
24560-163	16mm	Nickel Plated	100	M2.5		Backplanes, Test Adapters

Table 2/2

Catalog Number	Torque
24560-148	0.3N·m
24560-147	0.3N·m
24560-161	0.3N·m
24560-135	1.3N·m
24571-372	2.4N·m
24571-371	2.4N·m
24560-178	
24560-162	
24560-163	

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**