

# Connection clamp with levers

Distribution Clamps for Distribution Box.



## FEATURES

Connection clamp with levers

For all conductor types

3 or 5 conductors

Up to 4.00 mm<sup>2</sup>

## SPECIFICATIONS

Table 1/2

| Catalog Number | Product Type | Color              | Ambient Temperature | Clamp Quantity | Depth  | Height |
|----------------|--------------|--------------------|---------------------|----------------|--------|--------|
| 20118-902      | Clamp        | Transparent, Green | 85°C max            | 3              | 18.8mm | 8.4mm  |
| 20118-903      | Clamp        | Transparent, Green | 85°C max            | 5              | 18.8mm | 8.4mm  |

Table 2/2

| Catalog Number | Material      | Max Current | Max Voltage | Package Quantity | Weight | Width  |
|----------------|---------------|-------------|-------------|------------------|--------|--------|
| 20118-902      | Polycarbonate | 20A         | 600V        | 10               | 2.5g   | 18.8mm |
| 20118-903      | Polycarbonate | 20A         | 600V        | 10               | 4g     | 30mm   |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause

product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Middle East & India

Dubai, United Arab  
Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**