

Varistar CP Base/Plinth Side

Sides trim to mount to Varistar CP base/plinth



FEATURES

Base/plinth sides, plain

SPECIFICATIONS

Product Type: Cabinet/Rack Base

Material: Steel

Table 1/2

| Catalog Number | Height | Depth | Package Quantity | Color | Color Code | Finish |
|----------------|--------|--------|------------------|------------|------------|---------------|
| 24630-077 | 100mm | 600mm | 1 | Black Grey | RAL 7021 | Powder Coated |
| 24630-083 | 100mm | 300mm | 1 | Black Grey | RAL 7021 | Powder Coated |
| 24630-043 | 200mm | 1200mm | 1 | Black Grey | RAL 7021 | Powder Coated |
| 24630-078 | 100mm | 800mm | 1 | Black Grey | RAL 7021 | Powder Coated |
| 24630-040 | 100mm | 1200mm | 1 | Black Grey | RAL 7021 | Powder Coated |
| 24630-080 | 200mm | 600mm | 1 | Black Grey | RAL 7021 | Powder Coated |
| 24630-042 | 200mm | 1100mm | 1 | Black Grey | RAL 7021 | Powder Coated |
| 24630-081 | 200mm | 800mm | 1 | Black Grey | RAL 7021 | Powder Coated |
| 24630-038 | 100mm | 1000mm | 1 | Black Grey | RAL 7021 | Powder Coated |
| 24630-079 | 100mm | 900mm | 1 | Black Grey | RAL 7021 | Powder Coated |
| 24630-084 | 200mm | 300mm | 1 | Black Grey | RAL 7021 | Powder Coated |
| 24630-039 | 100mm | 1100mm | 1 | Black Grey | RAL 7021 | Powder Coated |
| 24630-082 | 200mm | 900mm | 1 | Black Grey | RAL 7021 | Powder Coated |

| Catalog Number | Height | Depth | Package Quantity | Color | Color Code | Finish |
|----------------|--------|--------|------------------|------------|------------|---------------|
| 24630-041 | 200mm | 1000mm | 1 | Black Grey | RAL 7021 | Powder Coated |

Table 2/2

| Catalog Number | Type | Package Unit |
|----------------|-------------|--------------|
| 24630-077 | Plinth Side | Pair |
| 24630-083 | Plinth Side | |
| 24630-043 | Plinth Side | Pair |
| 24630-078 | Plinth Side | Pair |
| 24630-040 | Plinth Side | Pair |
| 24630-080 | Plinth Side | Pair |
| 24630-042 | Plinth Side | Pair |
| 24630-081 | Plinth Side | Pair |
| 24630-038 | Plinth Side | Pair |
| 24630-079 | Plinth Side | Pair |
| 24630-084 | Plinth Side | |
| 24630-039 | Plinth Side | Pair |
| 24630-082 | Plinth Side | Pair |
| 24630-041 | Plinth Side | Pair |

ADDITIONAL PRODUCT DETAILS

Please order base/plinth for front/rear separately.

Cannot be used in conjunction with castors

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations

+1.763.422.2661

Chat with us:

nvent.com/schroff

Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

nvent.com/schroff

Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

nvent.com/schroff

Middle East & India

Dubai, United Arab

Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

nvent.com/schroff



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE