

LHX+ Control Unit



The Control Unit enriches the LHX+. It connects to the LHX+ sensors and the motorized coolant valve 23130-607. This enables the cooler to control the coolant air flow based on a chilled (supply) air temperature setpoint. It provides advanced remote monitoring functionality and various setup features.

FEATURES

Coolant flow control based on chilled (supply) air temperature setpoint. More control features with water control package

Separate, compact 19" control unit without loose wires in upper cabinet section

Clearly marked plug & play sensor connections

SPECIFICATIONS

- Rack Height:** 2U
- Product Type:** Control Unit
- Material:** Steel

Table 1/2

| Catalog Number | Height | Depth | Works With | Package Quantity | Color | Color Code |
|----------------|--------|-------|--------------------------|------------------|------------|------------|
| 23130-668 | 88mm | 220mm | Varistar, Varistar CP | 1 | Black Grey | RAL 7021 |
| 23130-664 | 88mm | 220mm | Varistar, Varistar CP | 1 | Black Grey | RAL 7021 |

Table 2/2

| Catalog Number | Finish | Input Voltage AC | Width |
|----------------|----------------------|------------------|---------|
| 23130-668 | Aluminum-Zinc Plated | 230V | 439.5mm |
| 23130-664 | Aluminum-Zinc Plated | 100 – 260V | 439.5mm |

ADDITIONAL PRODUCT DETAILS

Optional external display.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE