

19" Cable Ducting

19" unit for easy and effective cable management (cable ducting).



CERTIFICATIONS



FEATURES

19" Front panel for cable ducting

SPECIFICATIONS

- Accessory Type:** Front panel
- Product Type:** Front Panel
- Material:** Steel

Table 1/3

| Catalog Number | Rack Height | Mounting | Package Quantity | Front Finish | Rear Finish | Color Code |
|----------------|-------------|----------------|------------------|--------------|-------------|------------|
| 20118-734 | 1U | Screw-on Front | 1 | Painted | Painted | RAL 7035 |
| 20118-767 | 1U | Screw-on Front | 1 | Painted | Painted | RAL 7021 |
| 20118-736 | 2U | Screw-on Front | 1 | Painted | Painted | RAL 7035 |
| 20118-768 | 2U | Screw-on Front | 1 | Anodized | Conductive | RAL 7021 |

Table 2/3

| Catalog Number | Depth | EMC Shielding | Finish | Height | Rack Width | Type |
|----------------|-------|---------------|---------------|--------|------------|-----------------|
| 20118-734 | 1.5mm | No | Powder Coated | 43.6mm | 95HP | 19" Front Panel |
| 20118-767 | 1.5mm | No | Powder Coated | 43.6mm | 95HP | 19" Front Panel |
| 20118-736 | 1.5mm | No | Powder Coated | 88.1mm | 95HP | 19" Front Panel |
| 20118-768 | 1.5mm | No | Powder Coated | 88.1mm | 95HP | 19" Front Panel |

Table 3/3

| Catalog Number | Width |
|----------------|-------|
| 20118-734 | 483mm |
| 20118-767 | 483mm |
| 20118-736 | 483mm |
| 20118-768 | 483mm |

ADDITIONAL PRODUCT DETAILS

Please order 19" assembly kit separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE