

Quick Release Fastener

1/4 rotary lock with defined stop.



CERTIFICATIONS



FEATURES

1/4 rotary lock with defined stop

Identification of locking position due to slot position

Vibration and shake proof

Qty 100 pieces

SPECIFICATIONS

| | |
|----------------------|----------------------------------|
| Works With: | Front Panels |
| Product Type: | Hardware Kit |
| Finish: | Nickel Plated |
| Material: | Steel; Zinc Alloy; Thermoplastic |

Table 1/2

| Catalog Number | Color | Package Quantity | Color Code | Depth | Height | Width |
|----------------|-------------|------------------|------------|--------|--------|-------|
| 21101-850 | Jet Black | 100 | RAL 9005 | 20.6mm | 6mm | 7mm |
| 21101-847 | Pebble Grey | 100 | RAL 7032 | 16.7mm | 6mm | 7mm |
| 21101-849 | Pebble Grey | 100 | RAL 7032 | 20.6mm | 6mm | 7mm |

| CatalogNumber | Color | Package Quantity | Color Code | Depth | Height | Width |
|---------------|-----------|------------------|------------|--------|--------|-------|
| 21101-848 | Jet Black | 100 | RAL 9005 | 16.7mm | 6mm | 7mm |

Table 2/2

| Catalog Number | Fastener Type |
|----------------|-----------------------|
| 21101-850 | Knurled, Slotted Head |
| 21101-847 | Slotted Head |
| 21101-849 | Knurled, Slotted Head |
| 21101-848 | Slotted Head |

ADDITIONAL PRODUCT DETAILS

Quick-release fasteners: mounting without threaded inserts.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE