We connect and protect

Intelligent iPDU, EN6450, 400 VAC, 3-PH, 16 A

Data Solutions

CATALOG NUMBER

EN6450

Modular, compact intelligent PDU with inlet metering. Ultra-Low Profile Design

FEATURES

- Enlogic EN6xxx Intelligent Power Distribution Units monitors input power and power of each individual outlet and offers remote switching of individual outlets, provides billing grade unit level monitoring
- High Visibility Data Display and Interactive Graphic Display
- Measure circuit breaker loads across redundant feeds to avoid accidental downtime
- Enables smart load balancing for power efficiency and maximized capacity utilization
- Gigabit Ethernet Interface and redundant Ethernet (10/100)
- iPDU DC power redundancy solution for up to 64 PDU's
- Toolless Hot-Swap Controller
- Input voltage 400 VAC, 3-phase
- C13, C19 outlets

PRODUCT ATTRIBUTES

- Product Family: Enlogic
- Type: Intelligent PDU
- Product Type: Socket Strip
- Socket Type: (24) C13/C15; (24) C13/C15/C19/C21
- Socket Quantity: 48
- Color: Black
- Circuit Breaker: No Circuit Breaker
- Switched Outlets: Yes
- Circuit Breaker Quantity: 0
- Power Rating: 11.5 kVA North America; 11.0 kVA International

Input Cable Location: Top Feed

Max Power Input: 11.5 / 11.0 kVA

Input Voltage: 380 – 415V

Phase: 3 PH

On/Off Switch Included: Yes

Nominal Voltage: 415V

Output Voltage: 208 – 230VAC

Plug Type: IEC 60309 520P6/516P6

Amperage (Derated Amperage): 20 A (16 A) North America; 16 A International

Removable Input Cable: No

Rack Units: 0U

Material: Steel

Finish: Powder Coated

Metering Type: Outlet

Height: 1490mm

Width: 56mm

Depth: 75mm

Weight: 12kg

Package Quantity: 1

Input Cable Length: 1.8m

ADDITIONAL PRODUCT DETAILS

Please order bracket for vertical mounting separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.