

Mains Cable



nVent SCHROFF Mains cable provides practical, universal fastening with variable attachment facilities. They are general in nature and fit in to different applications like Fans, cabinet lights, etc., Industrial PC connections, Uninterruptible power supplies, Systems.

CERTIFICATIONS



FEATURES

Applications: Fans, cabinet lights, Industrial PC connections, Uninterruptible power supplies and Systems

SPECIFICATIONS

Product Type: Cable

Table 1/2

| Catalog Number | Input Connector | Output Connector | Length | Package Quantity | Color | Connector Type |
|----------------|-----------------------|------------------|--------|------------------|-------|----------------|
| 62150-191 | SCHUKO / UTE | IEC C13 | 2500mm | 1 | Black | Straight |
| 60704-020 | SCHUKO / UTE | IEC C13 | 2500mm | 1 | Grey | Angled |
| 60103-131 | SCHUKO / UTE | IEC C13 | 2500mm | 1 | Grey | Straight |
| 60110-361 | IEC C14 | IEC C13 | 1000mm | 1 | Black | Straight |
| 60197-053 | IEC C14 | IEC C13 | 2500mm | 1 | Black | Straight |
| 60110-360 | IEC C14 | IEC C13 | 500mm | 1 | Black | Straight |
| 60103-137 | BS = British Standard | IEC C13 | 2500mm | 1 | Black | Straight |

| Catalog Number | Input Connector | Output Connector | Length | Package Quantity | Color | Connector Type |
|----------------|------------------|------------------|--------|------------------|-------|----------------|
| 60103-141 | US = US Standard | IEC C13 | 2500mm | 1 | Black | Straight |

Table 2/2

| Catalog Number | Material |
|----------------|----------|
| 62150-191 | PVC |
| 60704-020 | PVC |
| 60103-131 | PVC |
| 60110-361 | PVC |
| 60197-053 | PVC |
| 60110-360 | PVC |
| 60103-137 | PVC |
| 60103-141 | PVC |

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE