

Washer

Washer used for PCB fixing.



CERTIFICATIONS



FEATURES

Washer

SPECIFICATIONS

Product Type: Washer

Type: Washer

Table 1/2

| Catalog Number | Material | Finish | Package Quantity | Accessory Type | Color | Height |
|----------------|-------------|--------|------------------|-------------------|-------|--------|
| 21101-964 | Polyamide 6 | | 100 | Mounting hardware | | |
| 21101-121 | Polyamide 6 | | 100 | Mounting hardware | White | 5mm |
| 21100-015 | ABS | | 50 | Mounting hardware | | |
| 21100-016 | ABS | | 100 | Mounting hardware | | |

| Catalog Number | Material | Finish | Package Quantity | Accessory Type | Color | Height |
|----------------|----------|---------------|------------------|-------------------|-------|--------|
| 21100-721 | Steel | Nickel Plated | 100 | Mounting hardware | | |

Table 2/2

| Catalog Number | Product Family | Width | Works With | Torque |
|----------------|---|-------|---|--------|
| 21101-964 | | | Front Panels, Eurorack, Novastar, Varistar, Varistar CP | 0.3N·m |
| 21101-121 | | 5mm | Backplanes | |
| 21100-015 | RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, Comptec, Inpac, MultipacPRO | | Front Panels, Eurorack, Novastar, Varistar, Varistar CP | |
| 21100-016 | RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, Comptec, Inpac, MultipacPRO | | Front Panels, Eurorack, Novastar, Varistar, Varistar CP | |
| 21100-721 | | | Front Panels, Frame Type Plug-In Unit | |

ADDITIONAL PRODUCT DETAILS

Quantity required for IEEE-Plug-in units (3U/6U)

Quantity required for plug-in units type 2 with extraction handle (3U/6U)

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations

+1.763.422.2661

Chat with us:

nvent.com/schroff

Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

nvent.com/schroff

Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

nvent.com/schroff



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE