

ProLine Solid Cover



Use a Solid Cover on the front or rear of the enclosure frame as a substitute for a door. Solid covers attach to the enclosure frame with semi-flush screws and include hangers for easy alignment of cover screws. They include a foam-in-place urethane gasket and two ground studs. Mounting hardware is included.

FEATURES

EMC covers are finished with paint over plated surfaces

SPECIFICATIONS

Table 1/3

| Catalog Number | Article Number | Material | Finish | Color | Color Code | Thickness |
|----------------|----------------|---------------------|---------|------------|------------|-----------|
| PCS207HF2 | 11809 | Mild Steel | | Light Gray | RAL 7035 | 1.52mm |
| PCS146SS | 31579 | Stainless Steel 304 | Brushed | | | 1.52mm |
| PCS76HF2 | 11689 | Mild Steel | | Light Gray | RAL 7035 | 1.52mm |
| PCS186 | 96430 | Mild Steel | | Light Gray | RAL 7035 | 1.52mm |
| PCS76 | 96360 | Mild Steel | | Light Gray | RAL 7035 | 1.52mm |
| PCS146HF2 | 11709 | Mild Steel | | Light Gray | RAL 7035 | 1.52mm |
| PCS204 | 25439 | Mild Steel | | Light Gray | RAL 7035 | 1.52mm |
| PCS76SS | 31559 | Stainless Steel 304 | Brushed | | | 1.52mm |
| PCS227 | 96520 | Mild Steel | | Light Gray | RAL 7035 | 1.52mm |
| PCS186HF2 | 11759 | Mild Steel | | Light Gray | RAL 7035 | 1.52mm |
| PCS184 | 29834 | Mild Steel | | Light Gray | RAL 7035 | 1.52mm |
| PCS206 | 96470 | Mild Steel | | Light Gray | RAL 7035 | 1.52mm |
| PCS146 | 96380 | Mild Steel | | Light Gray | RAL 7035 | 1.52mm |
| PCS226SS | 31679 | Stainless Steel 304 | Brushed | | | 1.52mm |
| PCS206HF2 | 11799 | Mild Steel | | Light Gray | RAL 7035 | 1.52mm |
| PCS226HF2 | 11839 | Mild Steel | | Light Gray | RAL 7035 | 1.52mm |
| PCS186SS | 31619 | Stainless Steel 304 | Brushed | | | 1.52mm |
| PCS166 | 96400 | Mild Steel | | Light Gray | RAL 7035 | 1.52mm |
| PCS226 | 96510 | Mild Steel | | Light Gray | RAL 7035 | 1.52mm |
| PCS126 | 29832 | Mild Steel | | Light Gray | RAL 7035 | 1.52mm |

Table 2/3

| Catalog Number | Article Number | Material | Finish | Color | Color Code | Thickness |
|----------------|----------------|---------------------|---------|------------|------------|-----------|
| PCS206SS | 31649 | Stainless Steel 304 | Brushed | | | 1.52mm |
| PCS166SS | 31599 | Stainless Steel 304 | Brushed | | | 1.52mm |
| PCS207 | 96480 | Mild Steel | | Light Gray | RAL 7035 | 1.52mm |
| PCS188 | 96450 | Mild Steel | | Light Gray | RAL 7035 | 1.9mm |
| PCS208 | 96490 | Mild Steel | | Light Gray | RAL 7035 | 1.9mm |
| PCS2010SS | 31669 | Stainless Steel 304 | Brushed | | | 1.9mm |
| PCS1810 | 96460 | Mild Steel | | Light Gray | RAL 7035 | 1.9mm |

| Catalog Number | Article Number | Material | Finish | Color | Color Code | Thickness |
|----------------|----------------|---------------------|---------|------------|------------|-----------|
| PCS148 | 96390 | Mild Steel | | Light Gray | RAL 7035 | 1.9mm |
| PCS228SS | 31689 | Stainless Steel 304 | Brushed | | | 1.9mm |
| PCS168 | 96420 | Mild Steel | | Light Gray | RAL 7035 | 1.9mm |
| PCS208HF2 | 11819 | Mild Steel | | Light Gray | RAL 7035 | 1.9mm |
| PCS208SS | 31659 | Stainless Steel 304 | Brushed | | | 1.9mm |
| PCS228 | 96530 | Mild Steel | | Light Gray | RAL 7035 | 1.9mm |
| PCS148HF2 | 11719 | Mild Steel | | Light Gray | RAL 7035 | 1.9mm |
| PCS209 | 29836 | Mild Steel | | Light Gray | RAL 7035 | 1.9mm |
| PCS2210 | 96540 | Mild Steel | | Light Gray | RAL 7035 | 1.9mm |
| PCS1810HF2 | 11789 | Mild Steel | | Light Gray | RAL 7035 | 1.9mm |
| PCS148SS | 31589 | Stainless Steel 304 | Brushed | | | 1.9mm |
| PCS78SS | 31569 | Stainless Steel 304 | Brushed | | | 1.9mm |
| PCS128 | 29833 | Mild Steel | | Light Gray | RAL 7035 | 1.9mm |

Table 3/3

| Catalog Number | Article Number | Material | Finish | Color | Color Code | Thickness |
|----------------|----------------|---------------------|---------|------------|------------|-----------|
| PCS78HF2 | 11699 | Mild Steel | | Light Gray | RAL 7035 | 1.9mm |
| PCS189 | 29835 | Mild Steel | | Light Gray | RAL 7035 | 1.9mm |
| PCS188SS | 31629 | Stainless Steel 304 | Brushed | | | 1.9mm |
| PCS78 | 96370 | Mild Steel | | Light Gray | RAL 7035 | 1.9mm |
| PCS2010 | 96500 | Mild Steel | | Light Gray | RAL 7035 | 1.9mm |
| PCS188HF2 | 11779 | Mild Steel | | Light Gray | RAL 7035 | 1.9mm |
| PCS2010HF2 | 11829 | Mild Steel | | Light Gray | RAL 7035 | 1.9mm |

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE