

## PCB Bracket



The PCB support brackets enable the fixing of a PCB to front panel. Available in different materials.

## CERTIFICATIONS



## FEATURES

For fixing PCB to front panel

## SPECIFICATIONS

**Product Type:** Bracket  
**Works With:** Front Panels  
**Type:** PCB Bracket

Table 1/2

| Catalog Number | Material                   | Package Quantity | Flammability Rating | Depth | Height | Width  |
|----------------|----------------------------|------------------|---------------------|-------|--------|--------|
| 60807-181      | Zinc Alloy                 | 1                |                     | 8.6mm | 11.1mm | 10.2mm |
| 60807-203      | Zinc Alloy                 | 1                |                     |       |        |        |
| 60807-183      | Polybutylene Terephthalate | 1                | UL® 94V-0           |       |        |        |
| 60807-011      | Lexan                      | 1                | UL® 94V-0           |       |        |        |
| 60807-211      | Polybutylene Terephthalate | 1                | UL® 94V-0           |       |        |        |

Table 2/2

| Catalog Number | Thread Size | Thread Type |
|----------------|-------------|-------------|
| 60807-181      | M2.5        | Metric      |
| 60807-203      |             |             |
| 60807-183      |             |             |
| 60807-011      |             |             |
| 60807-211      |             |             |

## ADDITIONAL PRODUCT DETAILS

Delivery is in standard pack multiples. Pricing is per individual item.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper

installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**