

# ProLine Containment System Hot Aisle Return Plenum

## Data Solutions



Works with a pod of cabinets surrounding a hot aisle. It is supported on top of the cabinets and channels the hot air exhausted from the server equipment housed inside the cabinets up to a ceiling plenum. This is used to completely separate the hot from cold air, drastically reducing data center energy costs.

It is designed to be sold as a build-to-order system that consists of side panels, end panels, and used with the ProLine Express Aisle Doors.

### INDUSTRY STANDARDS

---

UL94

### FEATURES

---

Drastically reduces data center energy costs

Reduces data center carbon footprint

Quick and simple installation

Custom built to facility specifications

Channels hot air from hot aisle to a facility ceiling plenum

Separates hot from cold air, preventing intermixing

Comes in 600mm, 750mm, 800mm and 1200mm widths

Built to match cabinet and facility ceiling height

Clean and aesthetic design

Panels can be field modified for cable entry

Designed to be assembled with only two tools (3mm and 8mm Allen keys)

Simple bolt attachment to cabinet top

Pairs with ProLine Aisle Containment sliding doors

### SPECIFICATIONS

---

Table 1/2

Catalog Number	Article Number	Height	Width	Depth	Material	Finish
PCPPB48	39376	20mm	1266mm	73mm	Aluminum	Anodized
PCPPS800	39373	1480mm	800mm	75mm	Polycarbonate	Transparent
PCPPS750	39372	1480mm	750mm	75mm	Polycarbonate	Transparent
PCPPS600	39371	1480mm	600mm	75mm	Polycarbonate	Transparent
PCPPS1200	39374	1480mm	1200mm	75mm	Polycarbonate	Transparent
PCPPE48	39375	1567mm	1307mm	89mm	Polycarbonate	Transparent

Table 2/2

Catalog Number	Article Number	Color	Color Code
PCPPB48	39376	Graphite Black	RAL 9011
PCPPS800	39373	Graphite Black	RAL 9011
PCPPS750	39372	Graphite Black	RAL 9011
PCPPS600	39371	Graphite Black	RAL 9011
PCPPS1200	39374	Graphite Black	RAL 9011
PCPPE48	39375	Graphite Black	RAL 9011

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**