

ProLine S1 Vertical Cable Managers

Data Solutions



Vertical Cable Managers are sold individually and attach to the cabinet rack angles. They provide a vertical open column for cables. Arrowhead fingers every 1.75 inch match rack unit spaces and allow for managing and protecting cables and ensuring proper bend radius. The engineered composite arrowhead supporting fingers are black plastic.

FEATURES

Vertical Cable Managers are sold individually and attach to the cabinet rack angles

They provide a vertical open column for cables

Arrowhead fingers every 1.75 inch match rack unit spaces and allow for managing and protecting cables and ensuring proper bend radius

The engineered composite arrowhead supporting fingers are black plastic

SPECIFICATIONS

Table 1/3

Catalog Number	Article Number	Height	Width	Depth	Material	Finish
PS1CM217	36753	79.03in	2.33in	8.36in	Mild Steel	Powder Coated
PS1CM127	36752	41.63in	2.33in	8.36in	Mild Steel	Powder Coated
PS1CM237	39237	81.97in	2.33in	8.36in	Mild Steel	Powder Coated
PS1CM238	39238	81.97in	4.3in	8.36in	Mild Steel	Powder Coated
PS1CM218	36754	79.03in	4.3in	8.36in	Mild Steel	Powder Coated

Table 2/3

Catalog Number	Article Number	Color	Color Code	Thickness	Vertical Cross Section	Vertical Cross Section Area
PS1CM217	36753	Jet Black	RAL 9005	14ga	1.76 x 8.18in	14.4in ²

Catalog Number	Article Number	Color	Color Code	Thickness	Vertical Cross Section	Vertical Cross Section Area
PS1CM127	36752	Jet Black	RAL 9005	14ga	1.76 x 8.18in	14.4in ²
PS1CM237	39237	Jet Black	RAL 9005	14ga	1.76 x 8.18in	14.4in ²
PS1CM238	39238	Jet Black	RAL 9005	14ga	3.72 x 8.18in	30.43in ²
PS1CM218	36754	Jet Black	RAL 9005	14ga	3.72 x 8.18in	30.43in ²

Table 3/3

Catalog Number	Article Number	Cable Quantity, 20-in. Diameter @70% Fill	Cable Quantity, 25-in. Diameter @75% Fill
PS1CM217	36753	343	220
PS1CM127	36752	343	220
PS1CM237	39237	343	220
PS1CM238	39238	726	464
PS1CM218	36754	726	464

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE