

STRAIGHT THROUGH JOINT



nVent PYROTENAX Straight Through Joint - NAM are a range of field installed, non fire-rated splice kits used to join MI copper-sheathed cables (with up to seven conductors), either where the manufactured length is shorter than the run length or for repair of damaged cables. If moisture is present, it must also be protected with a moisture protection kit.

FEATURES & BENEFITS

Simple to install

Reliable during long life: 30 year product warranty available

SPECIFICATIONS

Material Brass

Voltage Rating 600 V

Max Operating Temperature 90 °C

Table 1/1	
Catalog Number	Suitable for Cable Type
STJ1/1-496	1/1-496
STJ1/1/0-512	1/1/0-512
STJ1/1/0-543/512	1/1/0-512 to 543/1
STJ1/10-277	1/10-277
STJ1/2-449	1/2-449
STJ1/2-449/465	1/2-449 to 465/1

Catalog Number	Suitable for Cable Type
STJ1/2/0-580	1/2/0-580
STJ1/2/0-580/590	1/2/0-580 to 590/1
STJ1/250-746	1/250-746
STJ1/3-449	1/3-449
STJ1/3/0-621	1/3/0-621
STJ1/3/0-621/637	1/3/0-621 to 637/1
STJ1/350-834	1/350-834
STJ1/4-402	1/4-402
STJ1/4/0-684	1/4/0-684
STJ1/4/0-684/699	1/4/0-684 to 699/1
STJ1/500-1000	1/500-1000
STJ1/6-340	1/6-340
STJ1/8-298	1/8-298

Material Brass

Voltage Rating 600 V

Max Operating Temperature 105 °C

Table 1/1	
Catalog Number	Suitable for Cable Type
STJ4/0-699/11/4	699/1 (4/0)
STJ2/1-975	2/1-975
STJ2/10-449	2/10-449
STJ2/12-402	2/12-402
STJ2/14-371	2/14-371
STJ2/16-246T	2/16-246T
STJ2/16-340	2/16-340
STJ2/16-364TS	2/16-364TS
STJ2/18-215T	2/18-215T
STJ2/18-324TS	2/18-324TS
STJ2/2-865	2/2-865
STJ3/10-480	3/10-480
STJ3/12-480	3/12-480

Catalog Number	Suitable for Cable Type
STJ3/14-387	3/14-387
STJ3/16-355	3/16-355
STJ3/3-834	3/3-834
STJ3/4-746	3/4-746
STJ3/6-621	3/6-621
STJ3/8-590	3/8-590
STJ4/10-590	4/10-590
STJ4/12-465	4/12-465
STJ4/14-465	4/14-465
STJ4/16-387	4/16-387
STJ4/6-730	4/6-730
STJ4/8-590	4/8-590
STJ7/10-621	7/10-621
STJ7/12-543	7/12-543
STJ7/14-496	7/14-496

North America

Tel +1.800.545.6258
 Fax +1.800.527.5703
thermal.info@nvent.com

Europe, Middle East, Africa

Tel +32.16.213.511
 Fax +32.16.213.604
thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688
 Fax +86.21.5426.3167
cn.thermal.info@nvent.com

Latin America

Tel +1.713.868.4800
 Fax +1.713.868.2333
thermal.info@nvent.com



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER

© 2022 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners.
 nVent reserves the right to change specifications without notice.