

Seismic Free-Stand DA Cabinet Type 3R 4 4X 12, 72x24x36, Brushed, SS304

Data Solutions

NÚMERO DE CATÁLOGO

D722436SDAS

Ideal where front or front and rear access is required. These enclosures have sturdy unibody construction and include 19-inch rack angles to support equipment. These enclosures are ideal for housing and protecting networking and communications equipment from corrosion, liquid, and seismic events. 36-inch wide models include integral, vertical cable management that supports copper and fiber networking cables.

NORMAS DA INDÚSTRIA

UL 508A Listed; Type 3R, 4, 4X, 12; File No. E61997
cUL Listed per CSA C22.2 No. 94; Type 3R, 4, 4X, 12; File No. E61997

NEMA/EEMAC Type 3R, 4, 4X, 12

E.I.A. RS310-D

CSA, File No. 42186, Type

IEC 60529, IP66

OSPHD Approved OPM -0248-13

NEBS-Telecordia GR-63-CORE Zone 4: Tested with 1000 lb. of equipment installed

Meets California Building Code (CBC) requirements



CARACTERÍSTICAS

Reinforced stainless steel construction protects networking/communication equipment from corrosion, liquid, and seismic activity

Six seismic bottom-mounting plates made of painted plated steel for 5/8-inch diameter anchors

Lifting eyes installed for ease of handling

Rack angles included are infinitely adjustable from front-to-rear supporting multiple networking/communication equipment configurations

36-inch wide models include integral, vertical, RU-aligned fingers for supporting copper and fiber networking cables

AC models available for heat management

Data pockets included for equipment information management/organization

CARATERÍSTICAS DO PRODUTO

Número do artigo: 35448

Altura: 1834mm

Largura: 613mm

Profundidade: 918mm

Material: Stainless Steel 304

Acabamento: Brushed #3

Espessura: 2.78mm

Rack Units: 32U

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.



O nosso forte portefólio de marcas:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE