

CPCI Serial Backplane



The nVent SCHROFF CompactPCI Serial backplanes support the highest data transfer rates with PCIe up to Gen 3, 10GbE, USB 3.0 and S-ATA Rev. 3.0

CERTIFICATIONS



CARACTERÍSTICAS

Conforms to PICMG CompactPCI Serial (CPCI-S.0 R2.0) specification

Utility connector on rear of backplane

Mechanical centering and keying/coding strip in stainless steel on every fully equipped front and rear slot

ESPECIFICAÇÕES

Table 1/2

Número de catálogo	Product Type	Number of Slots	Rack Height	Backplane Type	System Slot	Slot Width
23007-661	Backplane	1	3U	CompactPCI Serial, No Bus		4HP
23007-641	Backplane	1	3U	CompactPCI Serial, No Bus		4HP
23007-681	Backplane	1	3U	CompactPCI Serial, No Bus		4HP
23007-621	Backplane	1	3U	CompactPCI Serial, No Bus		4HP

Número de catálogo	Product Type	Number of Slots	Rack Height	Backplane Type	System Slot	Slot Width
23007-679	Backplane	9	3U	CompactPCI Serial with Ethernet Star	Right	4HP
23007-668	Backplane	8	3U	CompactPCI Serial with Ethernet Star	Left	4HP
23007-629	Backplane	9	3U	CompactPCI Serial with Ethernet Star	Left	4HP
23007-669	Backplane	9	3U	CompactPCI Serial with Ethernet Star	Left	4HP
23007-676	Backplane	6	3U	CompactPCI Serial with Ethernet Star	Right	4HP
23007-677	Backplane	7	3U	CompactPCI Serial with Ethernet Star	Right	4HP
23007-628	Backplane	8	3U	CompactPCI Serial with Ethernet Star	Left	4HP
23007-636	Backplane	6	3U	CompactPCI Serial with Ethernet Star	Right	4HP
23007-627	Backplane	7	3U	CompactPCI Serial with Ethernet Star	Left	4HP
23007-682	Backplane	2	3U	CompactPCI Serial with Ethernet Full-mesh	Left	4HP
23007-683	Backplane	3	3U	CompactPCI Serial with Ethernet Full-mesh	Left	4HP
23007-667	Backplane	7	3U	CompactPCI Serial with Ethernet Star	Left	4HP
23007-695	Backplane	5	3U	CompactPCI Serial with Ethernet Full-mesh	Right	4HP

Número de catálogo	Product Type	Number of Slots	Rack Height	Backplane Type	System Slot	Slot Width
23007-655	Backplane	5	3U	CompactPCI Serial with Ethernet Full-mesh	Right	4HP
23007-637	Backplane	7	3U	CompactPCI Serial with Ethernet Star	Right	4HP
23007-654	Backplane	4	3U	CompactPCI Serial with Ethernet Full-mesh	Right	4HP

Table 2/2

Número de catálogo	Product Type	Number of Slots	Rack Height	Backplane Type	System Slot	Slot Width
23007-653	Backplane	3	3U	CompactPCI Serial with Ethernet Full-mesh	Right	4HP
23007-639	Backplane	9	3U	CompactPCI Serial with Ethernet Star	Right	4HP
23007-649	Backplane	9	3U	CompactPCI Serial with Ethernet Full-mesh	Left	4HP
23007-645	Backplane	5	3U	CompactPCI Serial with Ethernet Full-mesh	Left	4HP
23007-644	Backplane	4	3U	CompactPCI Serial with Ethernet Full-mesh	Left	4HP
23007-643	Backplane	3	3U	CompactPCI Serial with Ethernet Full-mesh	Left	4HP
23007-642	Backplane	2	3U	CompactPCI Serial with Ethernet Full-mesh	Left	4HP

Número de catálogo	Product Type	Number of Slots	Rack Height	Backplane Type	System Slot	Slot Width
23007-685	Backplane	5	3U	CompactPCI Serial with Ethernet Full-mesh	Left	4HP
23007-605	Backplane	5	3U	CompactPCI Serial with Ethernet Full-mesh	Right	4HP
23007-689	Backplane	9	3U	CompactPCI Serial with Ethernet Full-mesh	Left	4HP
23007-684	Backplane	4	3U	CompactPCI Serial with Ethernet Full-mesh	Left	4HP
23007-693	Backplane	3	3U	CompactPCI Serial with Ethernet Full-mesh	Right	4HP
23007-615	Backplane	5	3U	CompactPCI Serial with Ethernet Full-mesh	Right	4HP
23007-694	Backplane	4	3U	CompactPCI Serial with Ethernet Full-mesh	Right	4HP

Table 1/2

Número de catálogo	Connector Type	Power Connector Type	Utility Connector Type	Largura	Quantidade por embalagem
23007-661	AirMax VS	Microfit	MicroMatch, 10-pin	19.3mm	1
23007-641	AirMax VS	Microfit	MicroMatch, 10-pin	19.3mm	1
23007-681	AirMax VS	Microfit	MicroMatch, 10-pin	19.3mm	1
23007-621	AirMax VS	Microfit	MicroMatch, 10-pin	19.3mm	1
23007-679	AirMax VS	Power Bugs for M4 Cable Lugs	MicroMatch, 10-pin	181.9mm	1

Número de catálogo	Connector Type	Power Connector Type	Utility Connector Type	Largura	Quantidade por embalagem
23007-668	AirMax VS	Power Bugs for M4 Cable Lugs	MicroMatch, 10-pin	161.6mm	1
23007-629	AirMax VS	Power Bugs for M4 Cable Lugs	MicroMatch, 10-pin	181.9mm	1
23007-669	AirMax VS	Power Bugs for M4 Cable Lugs	MicroMatch, 10-pin	181.9mm	1
23007-676	AirMax VS	Power Bugs for M4 Cable Lugs	MicroMatch, 10-pin	120.9mm	1
23007-677	AirMax VS	Power Bugs for M4 Cable Lugs	MicroMatch, 10-pin	141.2mm	1
23007-628	AirMax VS	Power Bugs for M4 Cable Lugs	MicroMatch, 10-pin	161.6mm	1
23007-636	AirMax VS	Power Bugs for M4 Cable Lugs	MicroMatch, 10-pin	120.9mm	1
23007-627	AirMax VS	Power Bugs for M4 Cable Lugs	MicroMatch, 10-pin	141.2mm	1
23007-682	AirMax VS	Power Bugs for M4 Cable Lugs	MicroMatch, 10-pin	39.6mm	1
23007-683	AirMax VS	Power Bugs for M4 Cable Lugs	MicroMatch, 10-pin	60mm	1
23007-667	AirMax VS	Power Bugs for M4 Cable Lugs	MicroMatch, 10-pin	141.2mm	1
23007-695	AirMax VS	Power Bugs for M4 Cable Lugs	MicroMatch, 10-pin	100.6mm	1
23007-655	AirMax VS	Power Bugs for M4 Cable Lugs	MicroMatch, 10-pin	100.6mm	1
23007-637	AirMax VS	Power Bugs for M4 Cable Lugs	MicroMatch, 10-pin	141.2mm	1
23007-654	AirMax VS	Power Bugs for M4 Cable Lugs	MicroMatch, 10-pin	80.3mm	1

Table 2/2

Número de catálogo	Connector Type	Power Connector Type	Utility Connector Type	Largura	Quantidade por embalagem
23007-653	AirMax VS	Power Bugs for M4 Cable Lugs	MicroMatch, 10-pin	60mm	1
23007-639	AirMax VS	Power Bugs for M4 Cable Lugs	MicroMatch, 10-pin	181.9mm	1
23007-649	AirMax VS	Power Bugs for M4 Cable Lugs	MicroMatch, 10-pin	191.9mm	1

Número de catálogo	Connector Type	Power Connector Type	Utility Connector Type	Largura	Quantidade por embalagem
23007-645	AirMax VS	Power Bugs for M4 Cable Lugs	MicroMatch, 10-pin	100.6mm	1
23007-644	AirMax VS	Power Bugs for M4 Cable Lugs	MicroMatch, 10-pin	80.3mm	1
23007-643	AirMax VS	Power Bugs for M4 Cable Lugs	MicroMatch, 10-pin	60mm	1
23007-642	AirMax VS	Power Bugs for M4 Cable Lugs	MicroMatch, 10-pin	19.3mm	1
23007-685	AirMax VS	Power Bugs for M4 Cable Lugs	MicroMatch, 10-pin	100.6mm	1
23007-605	AirMax VS	PwrBlade	MicroMatch, 10-pin	159.9mm	1
23007-689	AirMax VS	Power Bugs for M4 Cable Lugs	MicroMatch, 10-pin	181.9mm	1
23007-684	AirMax VS	Power Bugs for M4 Cable Lugs	MicroMatch, 10-pin	80.3mm	1
23007-693	AirMax VS	Power Bugs for M4 Cable Lugs	MicroMatch, 10-pin	60mm	1
23007-615	AirMax VS	PwrBlade	MicroMatch, 10-pin	159.9mm	1
23007-694	AirMax VS	Power Bugs for M4 Cable Lugs	MicroMatch, 10-pin	80.3mm	1

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

North America

All locations

+1.763.422.2661

Chat with us:

nvent.com/schroff

Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

nvent.com/schroff

Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

nvent.com/schroff

Middle East & India

Dubai, United Arab

Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

nvent.com/schroff



O nosso forte portefólio de marcas:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE