

Mains Cable



nVent SCHROFF Mains cable provides practical, universal fastening with variable attachment facilities. They are general in nature and fit in to different applications like Fans, cabinet lights, etc., Industrial PC connections, Uninterruptible power supplies, Systems.

CERTIFICATIONS



CARACTERISTICAS

Applications: Fans, cabinet lights, Industrial PC connections, Uninterruptible power supplies and Systems

ESPECIFICAÇÕES

Product Type: Cable

Table 1/2

Número de catálogo	Input Connector	Output Connector	Length	Quantidade por embalagem	Cor	Connector Type
62150-191	SCHUKO / UTE	IEC C13	2500mm	1	Black	Straight
60704-020	SCHUKO / UTE	IEC C13	2500mm	1	Grey	Angled
60103-131	SCHUKO / UTE	IEC C13	2500mm	1	Grey	Straight
60110-361	IEC C14	IEC C13	1000mm	1	Black	Straight
60197-053	IEC C14	IEC C13	2500mm	1	Black	Straight
60110-360	IEC C14	IEC C13	500mm	1	Black	Straight
60103-137	BS = British Standard	IEC C13	2500mm	1	Black	Straight

Número de catálogo	InputConnector	Output Connector	Length	Quantidade por embalagem	Cor	ConnectorType
60103-141	US = US Standard	IEC C13	2500mm	1	Black	Straight

Table 2/2

Número de catálogo	Material
62150-191	PVC
60704-020	PVC
60103-131	PVC
60110-361	PVC
60197-053	PVC
60110-360	PVC
60103-137	PVC
60103-141	PVC

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



O nosso forte portefólio de marcas:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE