

# Mains Cable



nVent SCHROFF Mains cable provides practical, universal fastening with variable attachment facilities. They are general in nature and fit in to different applications like Fans, cabinet lights, etc., Industrial PC connections, Uninterruptible power supplies, Systems.

## CERTIFICATIONS



## CARACTERISTICAS

Applications: Fans, cabinet lights, Industrial PC connections, Uninterruptible power supplies and Systems

## ESPECIFICAÇÕES

**Product Type:** Cable

Table 1/2

| Número de catálogo | Input Connector       | Output Connector | Length | Quantidade por embalagem | Cor   | Connector Type |
|--------------------|-----------------------|------------------|--------|--------------------------|-------|----------------|
| 62150-191          | SCHUKO / UTE          | IEC C13          | 2500mm | 1                        | Black | Straight       |
| 60704-020          | SCHUKO / UTE          | IEC C13          | 2500mm | 1                        | Grey  | Angled         |
| 60103-131          | SCHUKO / UTE          | IEC C13          | 2500mm | 1                        | Grey  | Straight       |
| 60110-361          | IEC C14               | IEC C13          | 1000mm | 1                        | Black | Straight       |
| 60197-053          | IEC C14               | IEC C13          | 2500mm | 1                        | Black | Straight       |
| 60110-360          | IEC C14               | IEC C13          | 500mm  | 1                        | Black | Straight       |
| 60103-137          | BS = British Standard | IEC C13          | 2500mm | 1                        | Black | Straight       |

| Número de catálogo | InputConnector   | Output Connector | Length | Quantidade por embalagem | Cor   | ConnectorType |
|--------------------|------------------|------------------|--------|--------------------------|-------|---------------|
| 60103-141          | US = US Standard | IEC C13          | 2500mm | 1                        | Black | Straight      |

Table 2/2

| Número de catálogo | Material |
|--------------------|----------|
| 62150-191          | PVC      |
| 60704-020          | PVC      |
| 60103-131          | PVC      |
| 60110-361          | PVC      |
| 60197-053          | PVC      |
| 60110-360          | PVC      |
| 60103-137          | PVC      |
| 60103-141          | PVC      |

## AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em [www.nVent.com](http://www.nVent.com) e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



O nosso forte portefólio de marcas:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**