We connect and protect

# Intelligent iPDU, EN6326, 230 VAC, 1-PH, 16 A

## Data Solutions

### NÚMERO DE CATÁLOGO

**EN6326**

Modular, compact intelligent PDU with inlet metering. Ultra-Low Profile Design

### CARACTERISTICAS

Enlogic EN6xxx Intelligent Power Distribution Units monitors input power and power of each individual outlet and offers remote switching of individual outlets, provides billing grade unit level monitoring

High Visibility Data Display and Interactive Graphic Display

Measure circuit breaker loads across redundant feeds to avoid accidental downtime

Enables smart load balancing for power efficiency and maximized capacity utilization

Gigabit Ethernet Interface and redundant Ethernet (10/100)

iPDU DC power redundancy solution for up to 64 PDU's

Toolless Hot-Swap Controller

Input voltage 230 VAC, 1-phase

C13, C19 outlets

### CARATERÍSTICAS DO PRODUTO

Família de produtos: Enlogic

Tipo: Intelligent PDU

Product Type: Socket Strip

Tipo de soquete: (20) C13; (4) C19

Socket Quantity: 24

Cor: Black

Circuit Breaker: 16 A, 1-pole, Hy-Mag

Switched Outlets: Sim

Circuit Breaker Quantity: 0

Input Cable Location: Top Feed

Input Voltage: 200 – 240V

Phase: 1 PH

Interrupt Rating: 5kAIC

Max Power Input: 3.68 kVA

Output Voltage: 200 – 240VAC

Amperage (Derated Amperage): 16 A

Plug Type: IEC 60309 316P6 (IP44)

Rack Units: 0U

Removable Input Cable: Não

Metering Type: Outlet

Quantidade por embalagem: 1

## DETALHES ADICIONAIS DO PRODUTO

Please order bracket for vertical mounting separately.

## AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

O nosso forte portefólio de marcas:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.