

DC Fan

Axial fan, 119 mm, with DC input. Replacement part for 1 U fan trays.



CERTIFICATIONS



CARACTERISTICI

Axial 119 mm DC fan, with plug for connection cable

SPECIFICAȚII

Table 1/2

Număr de catalog	Works With	Width	Length	Height	Voltage DC	Airflow
60713-600	19" Fan Trays	119mm	119mm	32mm	12V	140m³/h
20713-242	19" Fan Trays	119mm	119mm	38mm	48V	184m³/h
20713-241	19" Fan Trays	119mm	119mm	38mm	12V	184m³/h
20713-240	19" Fan Trays	119mm	119mm	38mm	24V	184m³/h
20713-172	19" Fan Trays	119mm	119mm	25.5mm	24V	171m³/h

Table 2/2

Număr de catalog	Noise Level	Power	Max Static Pressure	Ambient Temperature	Package Quantity
60713-600	39dB(A)	8W	46Pa	70°C	1
20713-242	42dB(A)	8W	68Pa	70°C	1

Număr de catalog	Noise Level	Power	Max Static Pressure	Ambient Temperature	Package Quantity
20713-241	42dB(A)	8W	68Pa	70°C	1
20713-240	42dB(A)	8W	68Pa	70°C	1
20713-172	50.5dB(A)	7W	50.5Pa	70°C	1

DETALII SUPLIMENTARE DESPRE PRODUS

Please order connection cable and protective grille separately.

AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Portofoliul nostru puternic de mărci:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE