

Grub Screw

For fixing the threaded insert in the horizontal rail.



CERTIFICATIONS



CARACTERISTICI

Grub screw

SPECIFICAȚII

Type: Grub Screw

Product Type: Screw

Table 1/2

Număr de catalog	Length	Package Quantity	Thread Size	Finish	Material	Product Family
21102-980	8mm	100	M2.5		Stainless Steel	
21100-276	8mm	100	M2.5	Nickel Plated	Oțel	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO

Număr de catalog	Length	Package Quantity	Thread Size	Finish	Material	Product Family
21100-646	8mm	100	M3	Nickel Plated	Oțel	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO

Table 2/2

Număr de catalog	Works With	Torque	Certifications
21102-980	Subracks, Cases, Chassis	0.37N·m	
21100-276	Subracks, Cases, Chassis		RoHS
21100-646	Subracks, Cases, Chassis		RoHS

AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Portofoliul nostru puternic de mărci:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE