

Rack Safety Plus, 3 U, 120 V AC, EMC Filter

NUMĂR DE CATALOG

21272-002



CARACTERISTICI

19", 3 U Power Distribution Unit with Emergency Stop function

Supplies AC mains power to electrical or electronic devices as a central power switch

120 V phase to neutral mains input

AC outputs with different connector types, switched by ON/OFF switch

Permanent AC Outputs (Service)

All outputs are protected by circuit breakers

The emergency stop function meets the requirements of EN 60947-5-1 and EN 60204-1 and is vandalism-proof

An additional external emergency stop push button can be connected to the system

UL pending

ATTRIBUTE PRODUS

Product Type: Power Distributor

Works With: Varistar CP; Novastar

Function: Emergency Stop

Input Voltage AC: 120V

Number of Phases: 1

EMC Filter: Yes

Surge Arrester: Yes

Inrush Current Limiter: No

Residual Current Device: No

Circuit Breaker Cover: No

Rack Height: 3U

Socket Type: NEMA 5-15R; NEMA 5-20R

Accessory Type: Power distribution accessories

Package Quantity: 1

DETALII SUPLIMENTARE DESPRE PRODUS

For exact configuration of optional features and example configuration please refer to the item(s) delivered table.

AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Portofoliul nostru puternic de mărci:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE