

Inpac Front Panel

The front panel can be assembled on to the Inpac Case.



CERTIFICATIONS



CARACTERISTICI

Al panel, 2.5 mm

SPECIFICAȚII

Depth:	2.5mm
Material:	Aluminiu
Finish:	Anodized
Works With:	Cases
Accessory Type:	Front panel
Product Type:	Front Panel
Product Family:	Inpac

Table 1/2

Număr de catalog	Rack Height	Package Quantity	Front Finish	Rear Finish	Treated Edges	EMC Shielding
30828-055	2U	1	Anodized	Anodized	No	No
30828-067	6U	1	Anodized	Anodized	No	No
30828-061	4U	1	Anodized	Anodized	No	No
30828-058	3U	1	Anodized	Anodized	No	No

Table 2/2

Număr de catalog	Height	Width
30828-055	76mm	437mm
30828-067	253.8mm	437mm
30828-061	165mm	437mm
30828-058	120.5mm	437mm

DETALII SUPLIMENTARE DESPRE PRODUS

The assembly kit for the front panel is included with the 19" chassis.

AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Portofoliul nostru puternic de mărci:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE