

# Interscale for Mini-ITX, Conduction Cooled

Small form factor case with integrated EMC-shielding and conduction cooling for Mini-ITX boards, based on the innovative and flexible nVent SCHROFF Interscale platform.



## CERTIFICATIONS



## CARACTERISTICI

Modular case consisting of 3 easy to assemble parts; body, top cover and front panel

Cutout for Mini ITX I/O panel, power connector (Phoenix Contact, 0710028) and power switch (Schurter, MCS 18 Front)

Integrated EMC protection

Other dimensions, cutout shapes or locations, and screen printing available

Rigid construction requires only four screws

Board mounting studs installed

Color RAL 7016

## SPECIFICAȚII

<b>Height:</b>	94mm
<b>Depth:</b>	189mm
<b>Material:</b>	Aluminiu
<b>Type:</b>	Desktop
<b>Product Family:</b>	Interscale
<b>Protection Rating:</b>	IP30
<b>Color Code:</b>	RAL 7016
<b>Product Type:</b>	Small Form Factor Case

Table 1/1

Număr de catalog	Design Feature	Package Quantity	Cooling	Color	Finish	Width
14830-005	10 mm Fins	1	Conduction Cooled	Anthracite Grey	Vopsit Pulbere	184mm
14830-006	20 mm Fins	1	Conduction Cooled	Anthracite Grey	Vopsit Pulbere	184mm

## DETALII SUPLIMENTARE DESPRE PRODUS

Only the listed Interscale accessories are compatible.

Modified or customized cases up on request.

## AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe [www.nvent.com](http://www.nvent.com) și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Portofoliul nostru puternic de mărci:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**